

Product: [BAT-C2-W01.01-F01-U01-A01](#) 

Life Cycle Status: Discontinued

Compact WLAN Client and AccessPoint with 11ac technology and rapid roaming.



Product Description

The BAT-C2's compact design and low weight are unprecedented in its class of ruggedized industrial WLAN devices. It is optimized for integration either into mobile units or stationary machines. When used as a mobile client it delivers fast roaming at an enterprise security level. When used stationary it allows for simple integration and automatic control of its AccessPoint functionality to deliver wireless access locally around a machine.

Technical Drawing



Technical Specifications

Product description

Type:	BAT-C2-W01.01-F01-U01-A01
Name:	BAT-C2 Europe
Part Number:	942249001
Port type and quantity:	1 Port: 10/100 BASE TX
Radio protocol:	IEEE 802.11a, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IEEE 802.11ac

Product Life Cycle

Life Cycle:	Discontinued - the product is no longer manufactured
Discontinuation Announcement Date:	2023-12-12
Last Order Date:	2024-06-01
Last Delivery Date:	2024-10-01
Last Service Date:	2029-12-01

More Interfaces

WLAN Antenna:	2x RP-SMA Female Socket
Ethernet:	M12 D-Coded Socket Female
Power Supply:	M12 A-Coded Socket Male

Power requirements

Power Loss Buffer:	min. 10 msec
Operating Voltage:	12 VDC .. 24 VDC (nominal), 9.6 VDC .. 32 VDC (max tolerances)

Software

Software features:	Filesystem to store custom data, QoS, QoS based on IP or Ports, GRE, MAC filter
Management:	Web Interface (HTTPS), IPv4, IPv6, Filesystem to store custom data, SNMP v1/v2/v3
Diagnostics:	DNS, Routing, System Log, Ping, Traceroute, Syslog
Configuration:	DHCP client, DHCP Server, Extendable via custom Python Scripts
Security:	IPSec, Firewall, User Permission Management
Routing:	Static, RIP, OSPF, 1:1 NAT, Port Forwarding

Ambient conditions

MTBF (Telecordia SR-332 Issue 3) @ 25°C:	1 207 342 h
Operating temperature:	-40+70 °C
Relative humidity (non-condensing):	1-95 %

Mechanical construction

Dimensions (WxHxD):	102 mm x 72 mm x 34.5 mm
Weight:	140 g
Housing:	Plastic (PC+ABS), fire safety UL 94 V-0
Protection class:	IP65 (when using matching connectors)

Mechanical stability

IEC 60068-2-6 vibration:	5 Hz ... 8,4 Hz with 3.5 mm Amplitude; 8.4 Hz ... 150 Hz with 1 g
IEC 60068-2-27 shock:	11 g at 11 ms

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD):	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field:	20 V/m (80 MHz - 1000 MHz), 10 V/m (1GHz - 3 GHz), 10 V/m (3 GHz - 6 GHz)
EN 61000-4-4 fast transients (burst):	2 kV power line, 1 kV data line (shielded)
EN 61000-4-5 surge voltage:	power line 1 kV (line/earth), 0,5 kV (Line/line); data line 1 kV (shielded)
EN 61000-4-6 Conducted Immunity:	10 V (150 kHz - 80 MHz); 1 kHz, 80 % AM

EMC emitted immunity

EN 55032:	Class A
-----------	---------

Approvals

Basis Standard:	CE Conformity, RED
Safety of industrial control equipment:	EN 61131

Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
------------	---

WLAN Access Point

Access Point Functionality:	Yes
Channel Restriction if Client is Deactivated:	1-13, 36-48
Security:	WPA/WPA2 Personal PSK

WLAN Client

802.11w - PMF:	Yes
Client / STA Functionality:	yes
Network Modes:	1:1 MAC Adoption, Bridging, NAT + Masquerading
Roaming Thresholds:	Yes
Security:	IEEE 802.1X - FAST, IEEE 802.1X - LEAP, IEEE 802.1X - PEAP, IEEE 802.1X - TLS, IEEE 802.1X - TTLS, Open, WEP, WPA/WPA2 Enterprise Radius 802.1X, WPA/WPA2 Personal PSK

WLAN Output Power

WLAN technology	Power load
Minimal Output Power	5 dBm
Granularity steps	1 dB
802.11b, 1 Mbps	16±2 dBm
802.11b, 11 Mbps	16±2 dBm
802.11g, 6 Mbps	14±2 dBm
802.11g, 54 Mbps	14±2 dBm
802.11a, 6 Mbps	14±2 dBm
802.11a, 54 Mbps	14±2 dBm
802.11n, MCS0, 2.4 GHz	13±2 dBm
802.11n, MCS7, 2.4 GHz	13±2 dBm
802.11n, MCS0, 5 GHz	13±2 dBm
802.11n, MCS7, 5 GHz	13±2 dBm
802.11ac, MCS8, 5 GHz	13±2 dBm
802.11ac, MCS9, 5 GHz	11±2 dBm

WLAN Typical Receive Sensitivity

802.11n, 2.4 GHz, 20 MHz, MCS0:	-93 dBm
802.11n, 2.4 GHz, 20 MHz, MCS7:	-74 dBm
802.11n, 5 GHz, 20 MHz, MCS0:	-92 dBm
802.11n, 5 GHz, 20 MHz, MCS7:	-74 dBm
802.11ac, 5 GHz, 20 MHz:	-70 dBm

WLAN Approvals

WLAN Approvals	Applicable
ETSI RED CE	Yes
ETSI - EN 300 328	Yes
ETSI - EN 301 893-1	Yes
ETSI - EN 301 489-1	Yes
ETSI - EN 301 489-17	Yes
ETSI - EN 302 502 (5.8 GHz)	-
ETSI - EN 300 440 (SRD)	-
FCC	-
SRRC	-

WLAN Countries

WLAN AccessPoints/Clients	Applicable	WLAN AccessPoints/Clients	Applicable
Australia	-	Japan	-
Austria	Yes	Latvia	Yes
Belgium	Yes	Lithuania	Yes
Brazil	-	Luxembourg	Yes
Bulgaria	Yes	Malaysia	-
Canada	-	Malta	Yes
China	-	Mexico	-
Croatia	Yes	Netherland	-
Cyprus	Yes	New Zealand	-
Czech Republic	Yes	Philippines	-
Denmark	Yes	Poland	Yes

Estonia	Yes	Portugal	Yes
Finland	Yes	Romania	Yes
France	Yes	Singapore	-
Germany	Yes	Slowakia	Yes
Great Britain	-	Slowenia	Yes
Greece	Yes	South Korea	-
Hungary	Yes	Spain	Yes
India	-	Sweden	Yes
Indonesia	-	Thailand	-
Ireland	Yes	USA	-
Italy	Yes	Vietnam	-

WLAN Channels

WLAN Approvals	Applicable
2.4GHz	1-11, 12, 13
Supported Bandwidth, 5GHz	20/40/80 Mhz
5GHz (U-NII-1), 36-48	Yes
5GHz (U-NII-2a), 52-64	Yes
5GHz (U-NII-2c), 100-116	Yes
5GHz (U-NII-2c), 120-128	Yes
5GHz (U-NII-2c), 132-140	-
5GHz (U-NII-2c), 144	-
5GHz (U-NII-3), 149-165	-

Scope of delivery and accessories

Accessories to Order Separately:	Ethernet Cable M12-RJ45, Ethernet Cable M12-M12, 942 046-001 BAT-ANT-RSMA-2AGN-R
Scope of delivery:	1x Device, 1x General Safety Instructions, 1x Power Connector

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html
Software Download:	https://hirschmann-support.belden.com/en-US/downloads
Technical Information:	https://hirschmann-support.belden.com/en/kb/bat-c2

History

Update and Revision:	Revision Number: 0.177 Revision Date: 03-25-2025
----------------------	--

Variants

Item #	Type
942249001	BAT-C2-Europe

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.