



Product: [BE41230](#)

Lead Wire, 0.2mm² Str BC, PVC Ins, 70°C

Product Description

7x0.2B PVC VDMS 70C

Technical Specifications

Product Overview

Suitable Applications:	IEC 189-3, VDMS 70C
------------------------	---------------------

Physical Characteristics (Overall)

Conductor

Stranding	Material	Cross Section	Construction n x D
Stranded	BC - Bare Copper	0.2 mm ²	7x0.20 mm

Conductor Count:	1
------------------	---

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness
Insulation	PVC - Polyvinyl Chloride	1.7 mm	0.08 mm	0.4 mm

Electrical Characteristics

Conductor DCR

Element	Max. Conductor DCR
Conductor(s)	87.2 Ohm/km

Standards

UL AWM Style Compliance:	N/A
Military Compliance:	N/A

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU CE Mark:	On label
EU RoHS Compliance Date (yyyy-mm-dd):	1998-01-01

Flammability, LS0H, Toxicity Testing

UL voltage rating:	N/A
--------------------	-----

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
BE41230.002400	Black	Reel	2,400 m	8719605025135
BE41230.005000	Black	Reel	5,000 m	8719605025142
BE41230.092400	Blue	Reel	2,400 m	8719605025234
BE41230.042400	Brown	Reel	2,400 m	8719605025180

BE41230.082400	Gray	Reel	2,400 m	8719605025227
BE41230.052400	Green	Reel	2,400 m	8719605025197
BE41230.062400	Orange	Reel	2,400 m	8719605025203
BE41230.072400	Red	Reel	2,400 m	8719605025210
BE41230.032400	Violet	Reel	2,400 m	8719605025173
BE41230.012400	White	Reel	2,400 m	8719605025159
BE41230.022400	Yellow	Reel	2,400 m	8719605025166

History

Update and Revision:	Revision Number: 0.137 Revision Date: 07-26-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.