



Product: [BE43802](#)

Railtuff ® 7, 4PR #24 Str TC, XLPE ins, S/FTP, LSNH Jkt, EN 45545 HL 1-3, ECE R118.03

Product Description

Railtuff ® 7, 4 Pair AWG 24 Tinned Copper - Stranded, XLP/XLPO, XLPE insulation, S/FTP - Overall Braid + Foil shielding, Crosslinked e-beam LSZH / FRNC jacket, EN 45545-2 HL 1-3, ECE R118.03

Technical Specifications

Product Overview

Suitable Applications:	For use in railway applications such as rolling stock, buses or other vehicles, cable meets the requirements of the relevant parts of international railway standards like DIN 5510-2, EN 50153, EN 50155, EN 50305 and EN 45545-2, ECE R118.03
------------------------	---

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs	No. of Elements
24 AWG	19x36	TC - Tinned Copper	4	8

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PO - Polyolefin (Foam)	1.45 mm (0.0571 in)	White & Blue, White & Orange, White & Green, White & Brown	eBeam Cross-Linked

Table Notes: Insulation OD tolerance +/- 0.05mm

Cable Core

Description
4 pairs twisted together

Inner Shield

Element	Shield Type	Material	Coverage
Individual Shielded Pair	Tape	Bi-Laminate (Alum+Poly)	100%

Table Notes: Aluminium facing outside

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	80%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant, Thermoset)	8.1 mm (0.32 in)

Table Notes: e-Beamed to Cross-link, cable meets smoke test of LU 1-085. Jacket OD +/- 0.3mm

Overall Cable Diameter (Nominal): 8.1 mm (0.32 in)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
95 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
25 ns/100m	78%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
1	2.9 dB/100m
4	5.6 dB/100m
10	8.8 dB/100m
16	11.1 dB/100m
31.2	15.6 dB/100m
62.5	22.3 dB/100m
100	28.5 dB/100m
300	51.3 dB/100m
500	67.9 dB/100m
600	75.1 dB/100m
1000	100.4 dB/100m

Table Notes: Limits below 4MHz are for information only. Values at 1000 MHz are for information only

Transfer Impedance

Frequency	Max. Transfer Impedance
1 MHz	Max. 5 mOhm/m
10 MHz	Max. 5 mOhm/m
30 MHz	Max. 30 mOhm/m
100 MHz	100 mOhm/m

Transfer Impedance Class: Grade 1

Table Notes: IEC 61156-6

Screening Class: Type I

Table Notes: Coupling attenuation

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C to +90°C	-25°C To +50°C	-40°C to +90°C

Bend Radius

Stationary Min.	Installation Min.
32 mm (1.3 in)	64 mm

Standards and Compliance

Environmental Suitability:	Indoor, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-2-25, UN ECE R118.03
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 7
ISO/IEC Compliance:	ISO/IEC 11801-1
CENELEC Compliance:	EN 45545-2, Segregation class according EN50174-2 = d
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark

History

Update and Revision: Revision Number: 0.246 Revision Date: 05-15-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
--------	-------	------------	--------	-----

BE43802 010500M	Black	Reel	500 m	6938935091807
BE43802.00500	Blue	Reel	500 m	8719605026576
BE43802 006500M	Blue	Reel	500 m	6938935091791

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.