



Product: [BE43906](#)

LIGHTNING CONTROL DMX512 PVC

Product Description

LIGHTNING CONTROL 2 PAIR 22AWG/0.34mm² DMX512 PVC

Technical Specifications

Product Overview

Suitable Applications:	DMX 512 lighting control applications
------------------------	---------------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Construction n x D
22	7x30	TC - Tinned Copper	7x0.25 mm

Conductor Count:	4
Total Number of Pairs:	2

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	PE - Polyethylene	1.35 mm	0.10 mm

Color Chart

Number	Color
Pair 1	White & Red
Pair 2	Green & Black

Outer Shield

Type	Material	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D	Drainwire Position
Braid	Tinned Copper (TC)	80%		TC - Tinned Copper	24	7x0.20 mm	Over foil, under braid
Tape	Bi-Laminate (Alum+Poly)	100%	9/23 µm				

Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance
PVC - Polyvinyl Chloride	6.80 mm	0.25 mm

Table Notes:	Flexible Matte Finish Sheath
--------------	------------------------------

Construction and Dimensions

Cabling

Description
2 pairs twisted

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. Outer Shield DCR
58 Ohm/km	15 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
70 pF/m	112 pF/m

Inductance

Nominal Inductance
0.68 μ H/m

Temperature Range

Storage Temperature Range:	-25°C To +70°C
Other Temp Range:	-5 to +70 °C

Mechanical Characteristics

Bulk Cable Weight:	61 kg/km
--------------------	----------

Standards

CPR Euroclass:	Fca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
BE43906.00250	Black	Reel	250 m	8719605026606
BE43906.00500	Black	Reel	500 m	8719605026613
BE43906.001000	Black	Reel	1,000 m	8719605026590

History

Update and Revision:	Revision Number: 0.182 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.