



Product: [BE43992](#)

RailTuff Cat 5(e), PROFINET, 0.5mm², EN 45545 HL 1-3.

[Request Sample](#)

Product Description

RailTuff Railway Approved Cat 5e, PROFINET, 0.5mm², Polyolefin Insulation and Premium Cross-linked Jacket, Heavy Shielded, DIN 5510-2 level 1 to 4, EN 50155 Flame Resistance acc EN 45545-2, IEC 60332-1-2, EN 50305 & IEC 60332-3-25 cat D, EN 45545-2 (Class R15 and R16 HL3), Oil Resistance.

Technical Specifications

Product Overview

Suitable Applications:	PROFINET Cat5e, For use in railway applications such as rolling stock, cable meets the requirements of the relevant parts of international railway standards like DIN 5510-2, EN 50153, EN 50155, EN 50305 and EN 45545-2.
------------------------	--

Construction Details

Conductor

Size	Stranding	Stranding Class	Material	No. of Pairs	No. of Elements
0.5 mm ²	19x0.18 mm	Class 5	TC - Tinned Copper	2	4

Table Notes:	IEC 60228 class 5
--------------	-------------------

Insulation

Material	Nom. Insulation Diameter	Color Code
PO - Polyolefin	2.20 mm (0.0866 in)	White & Blue & Yellow & Orange
		1 Quad

Cable Core

Description
1 quad with center filler

Inner Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant, Thermoset)

Table Notes:	Bedding
--------------	---------

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	
Braid	Tinned Copper (TC)	80%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant, Thermoset)	8.0 mm (0.31 in)

Table Notes:	e-Beamed to Cross-link
--------------	------------------------

Overall Cable Diameter (Nominal):	8.0 mm (0.31 in)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Nom. Characteristic Impedance
--------------------	-------------------------------

40.1 Ohm/km (12.2 Ohm/1000ft) 100 Ohm

Delay

Nom. Velocity of Prop.
66%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. FEXT [dB]
1	2.1	65.3	64
4	4.1	56.3	52
10	6.5	50	44
16	8.3	47	40
31.25	11.7	42.9	33.9
62.5	17	38.4	28
100	22	35.3	24

Table Notes: EN 50288-2-2 and ISO/IEC 11801 ed. 2.0, Cat. 5e

Transfer Impedance

Frequency	Max. Transfer Impedance
10 Mhz	Max. 200 mOhm/m

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C to +90°C	-25°C To +50°C	-40°C to +90°C

Bend Radius

Stationary Min.	Installation Min.
40 mm (1.6 in)	80 mm (3.1 in)

Bulk Cable Weight: 68 kg/km (46 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-25
Data Category:	Category 5e
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 70%
CENELEC Compliance:	EN 45545-2
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark

History

Update and Revision: Revision Number: 0.34 Revision Date: 05-23-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
BE43992.00500	Black	Reel	500 m	8719605026682

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.