



**Part Number:** BE46380

**SPEAKERCABLE PVC 2x4.0mm<sup>2</sup>**

**Product Description**

SPEAKERCABLE PVC 2x4.0mm<sup>2</sup>

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor - Euroclass Eca
Suitable Applications:	Speaker cable

**Physical Characteristics (Overall)**

**Conductor**

Stranding	Material	Cross Section	Construction n x D
Stranded	BC - Bare Copper	4.00 mm <sup>2</sup>	56x0.30 mm
Conductor Count:		2	
Conductor Size:		4.00 mm <sup>2</sup>	

**Insulation**

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	PVC - Polyvinyl Chloride	3.50 mm	0.07 mm

**Color Chart**

Number	Color
Wire 1	Black
Wire 2	Red

**Outer Jacket Material**

Material	Color	Nominal Diameter	Diameter +/- Tolerance
Flexible PVC with matte finish	Gray (like RAL 7000) or Black	9.00 mm	0.10 mm

**Construction and Dimensions**

**Cabling**

Description
2 wires twisted

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR
4.5 Ohm/km

**Voltage**

Voltage Rating [V]
300 V

## Temperature Range

Storage Temp Range:	-15°C To +60°C
Other Temp Range:	-5 to +60 °C

## Standards

CPR Euroclass:	Eca
----------------	-----

## Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
---------------------------------------	------------

## Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2
-----------------------	---------------

## Part Number

### Variants

Item #	Color	Length
BE46380.01100	Black	100 m
BE46380.011000	Black	1,000 m
BE46380.00100	Gray	100 m
BE46380.00500	Gray	500 m

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.