



**Product:** [BE46383](#)

Speaker Cable PVC 4x4.0mm<sup>2</sup>, CPR Eca.

## Product Description

Speaker Cable, 4 Conductor 4.0mm<sup>2</sup> (56 x 0.30mm) Oxygen-Free Bare Copper (High Conductivity), PVC Insulation, PVC Jacket, Flexible, CPR Euroclass Eca.

## Technical Specifications

### Product Overview

Suitable Applications:	Auditorium, Stadium, Race Track, Church, Temple, Synagogue, Place Of Assembly, Casino, Sound
------------------------	--

### Construction Details

#### Conductor

Size	Stranding	Material
4 mm <sup>2</sup>	Stranded	BC - Bare Copper

#### Insulation

Material	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	3.50 mm (0.138 in)	Black, Red, White, Green

#### Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	11.00 mm (0.4331 in)

Table Notes:	Flexible Matte Finish Sheath
Overall Cable Diameter (Nominal):	11.00 mm (0.4331 in)

### Electrical Characteristics

#### Electricals

Max. Conductor DCR
4.5 Ohm/km (1.4 Ohm/1000ft)

### Mechanical Characteristics

#### Temperature

Operating	Storage
-15°C To +60°C	-15°C To +60°C

### Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2)
UK Regulation Compliance:	UKCA Mark

### History

Update and Revision:	Revision Number: 0.166 Revision Date: 02-03-2025
----------------------	--

## Part Numbers

---

### Variants

Item #	Color	Putup Type	Length	EAN
BE46383.00305	Black	Reel	305 m	8719605027603

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.