




Product: [BHVHLXX](#) 

Belden High Density Vertical Cable Managers

Product Description

Double-Sided High/Low Density Vertical Cable Managers (See table below for part numbers)

Technical Drawing



Technical Specifications

Application

Product Overview:	Modular High-Density Racking System (HDRS) for network cross-connect. HDRS is a well-engineered cross connect and hosting platform that offers you a high level of versatility and flexibility in systems design for ultimate network density and management. High-Density vertical manager half door allows easy cable access and hinging of the doors to both right and left side.
Benefits:	One standard hand tools are required for quick installation and simple field reconfiguration and modification. Designed to work seamlessly with Belden IBDN copper and fiber systems, cable management fingers align with the rack RUs for easy routing of patch cords to vertical managers, eliminating the need for horizontal managers. High level of modularity enables ease of removal of reconfiguring Belden's wide selection of accessories and components. Interchangeable cable retention gates, doors, fingers and accessories adapt to specific needs
Features:	Available in high or low density, finger sections can be easily removed during reconfigurations and easily replaced as needed. High-density 11RU sections are riveted into the vertical managers and align with the rack units. Designed to handle both copper and optical fiber structured cable networks, 1/4" diameter mounting holes along length of each vertical manager enable easy attachment of accessories, like cable bundle fasteners. Cable can be easily routed from one patch panel to another within the same rack, to the back of the rack or to an adjacent rack while still maintaining proper cable bend radius.
Environmental Space:	Indoor

Construction and Dimensions

Rack Units:	45U
Depth:	18.54 in

Mechanical Characteristics

Mounting:	Vertical
-----------	----------

Environmental and Overall Characteristics

Finish:	Black Powdercoat
Material:	6063-T6 Aluminum & Black Plastic
Color:	Black

Related Part Numbers

Included Parts:	Mounting Hardware
Packaging:	Individually Boxed

Variants

Part #	Height	Width	Depth	Weight
BHVHL03	79.63 in	3.6 in	18.54 in	42.0 lb
BHVHL06	79.63 in	6.0 in	18.54 in	44.0 lb
BHVHL10	79.63 in	10.0 in	18.54 in	50.0 lb
BHVHL12	79.63 in	12.0 in	18.54 in	54.0 lb

Update and Revision:	Revision Number: 0.246 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.