



**Product:** [BRSCCS 4D/9A](#)

M1M12 Field Attachable Connector, slim metal housing, IP67, male, 4-pole, D coded, shielded, straight, suited for rail application acc. to EN45545, Cat5e

**Product Description**

M12 Field Attachable Connector, slim metal housing, IP67, male, 4-pole, D coded, shielded, straight, suited for rail application acc. to EN45545, Cat5e

**Technical Specifications**

**Technical Data**

Product Family:	Data Connector
Brand:	Belden
Connector Type:	Field attachable
Type of Contact / Gender:	male
Connector Design:	straight
Number of Pins:	4 (included in the packaging)
Coding:	D
Shielding:	Shielded
Attachment Type:	Coupling Screw
Rated Voltage:	50 V AC / 60 V DC
Rated Impulse Voltage:	2,5 kV
Rated Current*:	4 A
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10 <sup>8</sup> Ohm
Mating Cycles:	> 100
Ambient Temperature (Operation)*:	-40°C to +85°C
Protection Degree / IP Rating**:	IP 67
Design Standard:	IEC 61076-2-101

**Materials**

Contact Base Material:	Cu Alloy
Contact Plating:	Cu/Au
Contact Bearer Material:	PA
Contact Bearer Color:	grey
Flammability Class (Contact Bearer):	UL 94 V-0
Housing Material:	CuZn
Housing Plating:	Ni
Housing Color:	silver
Cable Gland Material:	CuZn
Cable Gland Plating:	Ni
Strain-Relief Material:	PA
Flammability Class (Strain Relief):	UL 94 V-0
Attachment Material:	CuZn
Attachment Plating:	Cu/Ni
Shielding Material:	CuZn, plating: Ni

Additional Technical Data

Fastening Torque (Contact Screw):	1.5 -2.0 Nm (max. 3.0Nm), hand-tight
-----------------------------------	--------------------------------------

Safety & Environmental Compliance

RoHS Compliant:	yes, with exeption
-----------------	--------------------

Notes

Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
-------------------------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.