



Product: [C5562](#)

Teck90 600V, 4+G C #10+12 Str BC, XLPE Ins M4, PVC Jkt, AIA Armor, Blk PVC Jkt, CSA HL SUN RES -40C

Product Description

Teck90 600V, 4+G Conductor 10+12AWG (7x18H) Bare Copper, XLPE Insulation M4 Color Code, PVC Inner Jacket, Aluminum Interlock Armor, Black PVC Outer Jacket, CSA HL SUN RES -40C

Technical Specifications

Product Overview

Suitable Applications:	CEC Power and Control Applications up to 600V
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	10 AWG	7x18	BC - Bare Copper
Ground Wire	1	12 AWG	7x20	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLP, XLPO, XLPE (Thermoset)	0.03 in (0.76 mm)	0.174 in mm	Red, Black, Blue, White
Ground Wire	No Insulation			

Outer Shield

Material
No Shield

Inner Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.531 in (13.5 mm)

Armor

Armor Type & Material	Diameter Over Armor
AIA - Aluminum Interlock Armor	0.756 in (19.2 mm)

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.048 in (1.2 mm)	0.852 in (21.6 mm)	Yes

Overall Cable Diameter (Nominal):	0.852 in (21.6 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	1.06 Ohm/1000ft	24 Amps per Conductor at 30°C
Ground Wire	1.68 Ohm/1000ft (5.51 Ohm/km)	

Voltage

Voltage Rating

600 V (TECK 90)

Mechanical Characteristics

Temperature

Operating	Installation
-40°C To +90°C	-25°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
8.81 in (224 mm)	8.81 in (224 mm)

Max. Pull Tension:	864 lbs (392 kg)
Bulk Cable Weight:	373 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
CEC / C(UL) Compliance:	TECK 90, HL
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.253 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Putup Type	UPC
C5562 01010000	Reel	612825283157
C5562 0102500	Reel	612825283171
C5562 0105000	Reel	612825283188
C5562 0107500	Reel	612825283195
C5562 0105000	Reel	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.