



Product: [C5534](#)

Teck90 600V, 6+G C #12+14 Str BC, XLPE Ins M4, PVC Jkt, AIA Armor, Blk PVC Jkt, CSA HL SUN RES -40C

Product Description

Teck90 600V, 6+G Conductor 12+14AWG (7x20H) Bare Copper, XLPE Insulation M4 Color Code, PVC Inner Jacket, Aluminum Interlock Armor, Black PVC Outer Jacket, CSA HL SUN RES -40C

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
12	7x20	BC - Bare Copper	6
14		BC - Bare Copper	1

Conductor Count:	6
------------------	---

Insulation

Material	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.03 in
No Insulation	

Color Chart

Number	Color
1	Black and Numbered 1
2	Black and Numbered 2
3	Black and Numbered 3
4	Black and Numbered 4
5	Black and Numbered 5
6	Black and Numbered 6

Inner Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.576 in

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.897 in

Construction and Dimensions

Armor

Type of Armor	Material	Diameter over Armoring
Interlocked	Aluminum	0.801 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
1.65 Ohm/1000ft

Current

Max. Recommended Current [A]

16 Amps per Conductor at 25°C

Voltage

Non-UL Voltage Rating

600 V RMS

Temperature Range

Installation Temp Range:	-25°C To +90°C
Non-UL Temp Rating:	90°C
Operating Temp Range:	-40°C To +90°C

Mechanical Characteristics

Bulk Cable Weight:	435 lbs/1000ft
Max. Pull Tension:	200 lbs
Min Bend Radius/Minor Axis:	10.5 in

Standards

NEC/(UL) Compliance:	N/A
----------------------	-----

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-01

Suitability

Suitability - Hazardous Locations:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

CSA Flammability:	FT4
UL voltage rating:	N/A

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Putup Type	UPC
C5534 01010000	Reel	612825282839
C5534 0102500	Reel	612825282846
C5534 0105000	Reel	612825282853

History

Update and Revision:	Revision Number: 0.102 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.