



Product: [CAT5e UTP CM Patch Cords](#)

DataConnect CAT5e UTP Patch Cords, CM

Product Description

DataConnect CAT5e UTP CM Non-Bonded Patch Cords

Technical Specifications

Product Overview

Suitable Applications:	Ethernet 10/ 100/ 1000BASE-T, 2.5G/ 5GBASE-T
------------------------	--

Physical Characteristics (Overall)

Total Number of Pairs:	4
Overall Nominal Diameter:	0.19 in
Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color
Boot	Elastomer	Translucent
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	1.040 in
Plug / Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilitties
Mated Connection	750 Cycles

Standards

UL Rating:	CM (Not Riser or Plenum)
ISO/IEC Compliance:	IEC 60603-7
Data Category:	Category 5e
TIA/EIA Compliance:	Category 5E - TIA 568.2-D, ISO/IEC 11801-1
IEEE Compliance:	IEEE 802.3at type 1 and 2 (PoE) up to 30W, IEEE 802.3bt type 3 and 4 (PoE) up to 100W, CISCO (UPOE) up to 60W, Power over HDBaseTTM (POH) up to 100W
Other Standards:	ANSI/TIA 1096-A (formerly FCC Part 68-F)

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed, UL 1863, UL File E77103
-----------------	---

Related Part Numbers

Related Parts:	DataConnect CAT5e Modular Jacks, DataConnect CAT5e Patch Panels
----------------	---

Variants

Item #	Color	Length
C543100002	Black	2 ft
C543100003	Black	3 ft
C543100004	Black	4 ft
C543100005	Black	5 ft
C543100006	Black	6 ft
C543100007	Black	7 ft
C543100008	Black	8 ft
C543100010	Black	10 ft
C543100020	Black	20 ft
C543106003	Blue	3 ft
C543106005	Blue	5 ft
C543106007	Blue	7 ft
C543106010	Blue	10 ft
C543108003	Gray	3 ft
C543108005	Gray	5 ft
C543108007	Gray	7 ft
C543108010	Gray	10 ft
C543108020	Gray	20 ft
C543105003	Green	3 ft
C543105005	Green	5 ft
C543105007	Green	7 ft
C543105010	Green	10 ft
C543105020	Green	20 ft
C543103003	Orange	3 ft
C543103005	Orange	5 ft
C543103007	Orange	7 ft
C543103010	Orange	10 ft
C543109003	White	3 ft
C543109005	White	5 ft
C543109007	White	7 ft
C543109010	White	10 ft
C543104003	Yellow	3 ft
C543104005	Yellow	5 ft
C543104007	Yellow	7 ft
C543104010	Yellow	10 ft

Product Notes

Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length.
-----------	---

History

Update and Revision:	Revision Number: 0.33 Revision Date: 06-01-2023
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.