



Product: [C6D9ZxyyzzzM](#)



CAT6 28AWG Small diameter Unshielded Copper Patch Cord, UTP, PVC

Product Description

CAT6 28AWG Small diameter Unshielded Copper Patch Cord, UTP, PVC

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building cabling. Support current and future Category6 & 5e applications, such as: 10Base-T, 100Base-TX and 1000Base-T.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
28	Stranded	BC - Bare Copper	4

Insulation

Material
PE - Polyethylene

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	3.8 mm

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Type
Plug	Unshielded Polycarbonate	RJ45
Boot	Polycarbonate	Snagless
Front Connection	Phosphor bronze plated with 1.27µm gold over 2.54µm nickel undercoat	Blades

Electrical Characteristics

Conductor DCR

Max. Conductor DCR
236 Ohm/km

Dielectric Strength:	750 V AC (RMS)
Current Rating:	1.5 A
Insulation Resistance:	5 G ohm*km
Rated Voltage:	30 V DC

Temperature Range

Installation Temperature Range:	0°C To +75°C
Operating Temperature Range:	-20°C To +75°C

Mechanical Characteristics

Plug /Jack Compatibility:	RJ45
---------------------------	------

Termination Interface

Termination	Connection	Durabilities
RJ45	Mated Connection	750 Cycles

Standards

ISO/IEC Compliance:	ISO/IEC 11801-1
Data Category:	Category 6
TIA/EIA Compliance:	TIA-568.2-D

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Related Part Numbers

Related Parts:	CAT6 Modular Jacks, CAT6 Patch Panels
----------------	---------------------------------------

Variants

Item #	Color	Length
C6D9Z1100D5M	Black	0.5 m
C6D9Z110001M	Black	1 m
C6D9Z110002M	Black	2 m
C6D9Z110003M	Black	3 m
C6D9Z110005M	Black	5 m
C6D9Z1060D5M	Blue	0.5 m
C6D9Z106001M	Blue	1 m
C6D9Z106002M	Blue	2 m
C6D9Z106003M	Blue	3 m
C6D9Z106005M	Blue	5 m
C6D9Z1010D5M	Brown	0.5 m
C6D9Z101001M	Brown	1 m
C6D9Z101002M	Brown	2 m
C6D9Z101003M	Brown	3 m
C6D9Z101005M	Brown	5 m
C6D9Z1050D5M	Green	0.5 m
C6D9Z105001M	Green	1 m
C6D9Z105002M	Green	2 m
C6D9Z105003M	Green	3 m
C6D9Z105005M	Green	5 m
C6D9Z1080D5M	Grey	0.5 m
C6D9Z108001M	Grey	1 m
C6D9Z108002M	Grey	2 m
C6D9Z108003M	Grey	3 m
C6D9Z108005M	Grey	5 m
C6D9Z1030D5M	Orange	0.5 m
C6D9Z103001M	Orange	1 m
C6D9Z103002M	Orange	2 m
C6D9Z103003M	Orange	3 m
C6D9Z103005M	Orange	5 m
C6D9Z1070D5M	Purple	0.5 m
C6D9Z107001M	Purple	1 m
C6D9Z107002M	Purple	2 m
C6D9Z107003M	Purple	3 m
C6D9Z107005M	Purple	5 m
C6D9Z1020D5M	Red	0.5 m

C6D9Z102001M	Red	1 m
C6D9Z102002M	Red	2 m
C6D9Z102003M	Red	3 m
C6D9Z102005M	Red	5 m
C6D9Z1090D5M	White	0.5 m
C6D9Z109001M	White	1 m
C6D9Z109002M	White	2 m
C6D9Z109003M	White	3 m
C6D9Z109005M	White	5 m
C6D9Z1040D5M	Yellow	0.5 m
C6D9Z104001M	Yellow	1 m
C6D9Z104002M	Yellow	2 m
C6D9Z104003M	Yellow	3 m
C6D9Z104005M	Yellow	5 m

History

Update and Revision:	Revision Number: 0.20 Revision Date: 07-03-2023
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.