



Product: [Ceiling](#)

## Ceiling Zone Enclosures



### Product Description

Ceiling Zone Enclosures

### Technical Specifications

#### Application

Product Overview:	Ceiling-or floor-based zone connectivity replaces traditional homeruns to telecom rooms. Feeder category cables or pre-terminated cables are directed to a central distribution point in the zone where they interconnect to individual cable runs that fan out to each workstation outlet.
Benefits:	2' x 2' / 2' x 4', Ceiling/floor, Active/passive, Removable Door, Zone connectivity provides a way to keep most cabling permanent and undisturbed while making moves, adds and changes (MAC's) easier
Features:	UL 50/UL 1863/ UL 2043, Prevents fire spread with fire-rated foam sealing kits, Supports simple front or back routing with edge-protected cable entry ports, Enclosures can support up to 70 lbs. including door load, Door will support 20 lb., Plenum rated
Environmental Space:	Indoor

#### Environmental and Overall Characteristics

Color:	White
--------	-------

#### Related Part Numbers

Packaging:	Individually Boxed
------------	--------------------

#### Variants

Part #	Width	Depth
XCAE244812-S01	8U Active Ceiling Enclosures w/NEMA Box-Access Ports	Active
XCPE242412-S02	Cable Consolidation Ceiling Enclosure for Wiring Blocks	Passive
XCPE244812-S01	4U Passive Ceiling Enclosure, 4 Access Ports	Passive
XCPE244812-S02	8U Passive Ceiling Enclosure, 4 Access Ports	Passive
XCAE242412-S01	7U Active Ceiling Enclosures w/NEMA Box-Access Ports	Active
XCPE242412-S01	5U Passive Ceiling Enclosure with Equipment Bracket	Passive

Update and Revision:	Revision Number: 0.104 Revision Date: 11-09-2022
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.