

**Part Number:** CAT 5E HDPP BIX 24 1U

CAT 5E HDPatch Panel, BIX 24 Port, 1U



## Product Description

CAT5E HD-BIX Patch Panel, 24-port, 1U

## Technical Specifications

### Product Overview

Environmental Space:	Indoor
Suitable Applications:	IBDN System 1200, TIA Category 5e, ISO Class D, 1000BASE-T, 100BASE-T

### Physical Characteristics (Overall)

Height:	1.75 in
Width:	19.000 in
Depth:	1.500 in
Port Count:	24 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	1.200 lbs

### Connectors

#### Materials

Description	Material
Panel	Steel

### Construction and Dimensions

Max Capacity:	24 connectors (preloaded)
---------------	---------------------------

### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 mOhm

### Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

### Mechanical Characteristics

Footprint/Type:	HDPP
Tool Compatibility:	BIX Connecting Tool (A0270165)
Plug /Jack Compatibility:	RJ45
Termination Type:	Universal T568A/B

## Standards

Data Category:	Category 5e
Telecommunications Standards:	Category 5 - ISO/IEC 11801:2002 Ed.2
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7

## Applicable Environmental and Other Programs

EU Directive 2011/65/EU (ROHS II):	Yes
MII Order #39 (China RoHS):	EUP 50

## Flammability, LS0H, Toxicity Testing

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

## Part Number

Related Parts:	CAT5E Modular Cords
----------------	---------------------

## Variants

Item #	Color	UPC
AX103260	Black	611589005784

## Product Notes

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet;, 1 Installation Guide
Notes:	For proper installation refer to Installation Guide PX100796 included with the product

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.