



## Product: [CAT6+ S/FTP LSZH PATCH CORDS](#)

Copper RJ45 Patch Cord, CAT6+ , S/FTP, LSZH

### Product Description

Copper RJ45 Patch Cord, CAT6+ , S/FTP, 26AWG, LSZH/FRNC

### Technical Specifications

#### Product Overview

Suitable Applications:	Horizontal and building cabling. Support current and future Category 6 and 5e applications, such as: 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Nominal Diameter	No. of Pairs
26	Stranded	6.1 mm	4

Total Number of Pairs:	4
------------------------	---

##### Insulation

Material
PE - Polyethylene

##### Inner Shield

Element	Type	Material
Individual Shielded Pair	Tape	Bi-Laminate (Alum+Poly)

##### Outer Shield

Type	Material	Coverage [%]
Braid	Tinned Copper (TC)	30%

##### Outer Jacket

Material	Nominal Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.1 mm

Wiring Scheme:	T568A/B-T568A/B
----------------	-----------------

Packaging:	Individually packaged in a clear plastic bag.
------------	---

#### Connectors

##### Materials

Description	Material	Type
Plug	Polycarbonate	RJ45
Boot	LSZH	Snagless
Front Connection	Phosphor Bronze with 50u inch Gold over Nickel Plating	Blades

#### Electrical Characteristics

Dielectric Strength:	2.5 kV DC
Current Rating:	1 A
Insulation Resistance:	5000 MOhm*km
Max Contact Resistance:	20 mOhm

## Voltage

### Voltage Rating [V]

72 V DC

Performance Footnote1: There is 1dB margin on NEXT and RL guaranteed compared to ISO/IEC 11801-1:2018

Performance Footnote2: The performance data below 4Mhz or above 500Mhz are for information only.

## Temperature Range

Installation Temperature Range: 0°C To +50°C

Operating Temperature Range: -20°C to +60°C

## Mechanical Characteristics

Min Bend Radius (Overall Cable): 25 mm

Plug /Jack Compatibility: RJ45

## Termination Interface

Termination	Connection	Durabilities
RJ45	Mated Connection	750 Cycles

## Standards

ISO/IEC Compliance: ISO/IEC 11801-1

Data Category: Category 6

TIA/EIA Compliance: ISO/IEC 11801-1:2017; EN 50173-1 Amd 1 Category 6; ANSI/TIA/EIA 568 C.2 Category 6

## Applicable Environmental and Other Programs

Environmental Space: Indoor Rated (Not Riser or Plenum)

## Suitability

Suitability - Indoor: Yes

## Flammability, LS0H, Toxicity Testing

IEC Flammability: IEC 60332-3-22

## Related Part Numbers

Related Parts: CAT 6+ Shielded Modular Jacks, CAT 6+ shielded Patch Panels

## Variants

Item #	Color	Length
C6S4100001M	Black	1 m
C6S4100002M	Black	2 m
C6S4100003M	Black	3 m
C6S4100005M	Black	5 m
C6S4100010M	Black	10 m
C6S4100015M	Black	15 m
C6S41000D5M	Black	0.5 m
C6S4106020M	Black	20 m
C6S4106070M	Black	70 m
C6S4106001M	Blue	1 m
C6S4106002M	Blue	2 m
C6S4106003M	Blue	3 m
C6S4106005M	Blue	5 m
C6S4106008M	Blue	8 m
C6S4106010M	Blue	10 m
C6S4106015M	Blue	15 m
C6S41060D5M	Blue	0.5 m
C6S4106006M	Blue	6 m
C6S4106025M	Blue	25 m
C6S4106030M	Blue	30 m
C6S4106035M	Blue	35 m
C6S4106040M	Blue	40 m
C6S4106045M	Blue	45 m

C6S4106050M	Blue	50 m
C6S4106055M	Blue	55 m
C6S4106060M	Blue	60 m
C6S4106065M	Blue	65 m
C6S4106080M	Blue	80 m
C6S4106085M	Blue	85 m
C6S4106090M	Blue	90 m
C6S4108001M	Gray	1 m
C6S4108002M	Gray	2 m
C6S4108003M	Gray	3 m
C6S4108005M	Gray	5 m
C6S4108010M	Gray	10 m
C6S4108015M	Gray	15 m
C6S41080D5M	Gray	0.5 m
C6S4108025M	Gray	25 m
C6S4108030M	Gray	30 m
C6S4105001M	Green	1 m
C6S4105002M	Green	2 m
C6S4105003M	Green	3 m
C6S4105005M	Green	5 m
C6S4105010M	Green	10 m
C6S4105015M	Green	15 m
C6S41050D5M	Green	0.5 m
C6S4103005M	Orange	5 m
C6S4102001M	Red	1 m
C6S4102002M	Red	2 m
C6S4102003M	Red	3 m
C6S4102005M	Red	5 m
C6S4102010M	Red	10 m
C6S4102015M	Red	15 m
C6S41020D5M	Red	0.5 m
C6S4107005M	Violet	5 m
C6S41071D5M	Violet	1.5 m
C6S4109070M	White	70 m
C6S41090D5M	White	0.5 m
C6S4109050M	White	50 m
C6S4109001M	White	1 m
C6S4109002M	White	2 m
C6S4109003M	White	3 m
C6S4109005M	White	5 m
C6S4109010M	White	10 m
C6S4109015M	White	15 m
C6S4109030M	White	30 m
C6S4104001M	Yellow	1 m
C6S4104002M	Yellow	2 m
C6S4104003M	Yellow	3 m
C6S4104005M	Yellow	5 m
C6S4104010M	Yellow	10 m
C6S4104015M	Yellow	15 m
C6S41040D5M	Yellow	0.5 m

## History

Update and Revision:	Revision Number: 0.104 Revision Date: 03-02-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.