



Product: [DCX-384F-RL](#)



DCX HOUSING 384F RIGHT-LEFT, W/8 TRAYS, TRUNK & PCORD MGT

Product Description

DCX HOUSING 384F-FIBER, RIGHT-LEFT CABLE FLOW, WITH 8 TRAYS, TRUNK & PATCH MANAGEMENT

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Optical Distribution Frame, Data Centers, Central Equipment Room |
|------------------------|--|

Construction

| | |
|---------|-----------|
| Weight: | 12.57 lbs |
| Height: | 6.729 in |
| Width: | 20.807 in |
| Depth: | 11.81 in |

Physical Specifications

| | |
|---------------|--|
| Max Capacity: | Holds 32 Cassettes/Frames, Base 12 or 48 Cassettes, Base-8 |
|---------------|--|

Mechanical Characteristics

| | |
|-------------------|-------------------------------------|
| Termination Type: | Front and Right Trunk Cables Access |
|-------------------|-------------------------------------|

Temperature Range

| | |
|------------------------------|----------------|
| Operating Temperature Range: | -10°C to +60°C |
| Storage Temperature Range: | -40°C to +70°C |

Product Material

Materials

| Description | Material | Color |
|-------------|---------------|-------|
| Housing | Steel | Black |
| Housing | PC/ABS | |
| Housing | Polycarbonate | |

Standards

| | |
|-----------------------------|--------|
| MII Order #39 (China RoHS): | EUP 50 |
|-----------------------------|--------|

Related Part Numbers

| | |
|----------------|---|
| Related Parts: | #12-24 machine screw Phillips (4x), Rail cage nuts (4x) |
|----------------|---|

Product Notes

| | |
|------------|---|
| Packaging: | Individually packaged in a cardboard box |
| Notes: | Use 144F and 288 Fiber Trunk is not recommended for this housing. For more information, please refer to our web site at http://www.belden.com . |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.50 Revision Date: 07-19-2024 |
|----------------------|---|

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.