



Product: [CAT6 UTP CM Patch Cords](#)

DataConnect CAT6 UTP Patch Cords, CM

Product Description

DataConnect CAT6 UTP CM 24 AWG Non-Bonded Patch Cords

Technical Specifications

Product Overview

Suitable Applications:	Ethernet 10/ 100/ 1000BASE-T, 2.5GBASE-T
------------------------	--

Physical Characteristics (Overall)

Total Number of Pairs:	4
Overall Nominal Diameter:	0.223 in
Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color
Boot	Elastomer	Translucent
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	1.040 in
Plug / Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilittes
Mated Connection	750 Cycles

Standards

UL Rating:	CM (Not Riser or Plenum)
ISO/IEC Compliance:	IEC 60603-7
Data Category:	Category 6
TIA/EIA Compliance:	Category 6 - TIA 568.2-D, ISO/IEC 11801-1, TIA TSB-5021
IEEE Compliance:	IEEE 802.3at type 1 and 2 (PoE) up to 30W, IEEE 802.3bt type 3 and 4 (PoE) up to 100W, CISCO (UPOE) up to 60W, Power over HDBaseTTM (POH) up to 100W

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed, UL 1863, UL File E77103
-----------------	---

Related Part Numbers

Related Parts:	DataConnect CAT6 Modular Jacks, DataConnect CAT6 Patch Panels
----------------	---

Variants

Item #	Color	Length
C643100002	Black	2 ft
C643100003	Black	3 ft
C643100004	Black	4 ft
C643100005	Black	5 ft
C643100006	Black	6 ft
C643100007	Black	7 ft
C643100008	Black	8 ft
C643100010	Black	10 ft
C643106002	Blue	2 ft
C643106003	Blue	3 ft
C643106004	Blue	4 ft
C643106005	Blue	5 ft
C643106006	Blue	6 ft
C643106007	Blue	7 ft
C643106008	Blue	8 ft
C643106010	Blue	10 ft
C643106015	Blue	15 ft
C643108004	Gray	4 ft
C643108003	Gray	3 ft
C643108005	Gray	5 ft
C643108007	Gray	7 ft
C643108010	Gray	10 ft
C643105005	Green	5 ft
C643105002	Green	2 ft
C643105003	Green	3 ft
C643105007	Green	7 ft
C643105010	Green	10 ft
C643103002	Orange	2 ft
C643103003	Orange	3 ft
C643103005	Orange	5 ft
C643103007	Orange	7 ft
C643103010	Orange	10 ft
C643107007	Violet	7 ft
C643107010	Violet	10 ft
C643109002	White	2 ft
C643109003	White	3 ft
C643109004	White	4 ft
C643109005	White	5 ft
C643109006	White	6 ft
C643109007	White	7 ft
C643109010	White	10 ft
C643104002	Yellow	2 ft

C643104003	Yellow	3 ft
C643104005	Yellow	5 ft
C643104007	Yellow	7 ft
C643104008	Yellow	8 ft
C643104010	Yellow	10 ft
C643104015	Yellow	15 ft

Product Notes

Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length.
-----------	---

History

Update and Revision:	Revision Number: 0.33 Revision Date: 02-29-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.