



Product: [CLAP4106002M](#)



LOCKABLE UTP PATCH CORD, LSZH BLUE 2.0M CAT6A T568B 4PR 26AWG

## Product Description

LOCKABLE UTP PATCH CORD, LSZH BLUE 2.0M CAT6A T568B 4PR 26AWG \*The key should be ordered separately (the key part number is AP100010-10).

## Technical Specifications

### Physical Characteristics (Overall)

#### Outer Jacket

Material	
LSZH - Low Smoke Zero Halogen (Flame Retardant)	
Wiring Scheme:	The wiring scheme can be customized both for T568A and T568B
Packaging:	1 unit packaged in a plastic bag.

### Connectors

#### Materials

Material
PC - Polycarbonate, UL 94V-2 rated
Phosphor bronze plated with 50u" gold over 100u" nickel undercoat

### Electrical Characteristics

Dielectric Strength:	1000 VAC (RMS)
Insulation Resistance:	500 MΩ min.
Max Contact Resistance:	20 mOhm
Rated Voltage:	72 VDC maximum

### Temperature Range

Operating Temperature Range:	-10 to + 60
------------------------------	-------------

### Mechanical Characteristics

#### Termination Interface

Durabilities
750 Cycles

### Standards

ISO/IEC Compliance:	ISO/IEC 11801:2002/Amd 2:2010
Data Category:	Category 6A

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	EU Directive 2002/95/EC (RoHS)

### Related Part Numbers

Related Parts:	KEY, CAT6A Modular Jacks, CAT6A Patch panels
----------------	--

## History

Update and Revision:	Revision Number: 0.9 Revision Date: 12-13-2024
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.