



Part Number: DHIP162U3B02C

Indoor Digital Electricity Hybrid Cable, OM3, 2 Breakout Fibers, #16-2pr, CMP-OF

Product Description

Indoor Digital Electricity Hybrid Cable, OM3, 2 Breakout Fibers, 3.0mm Sub-units, 2- 16 AWG Pairs, Plenum

Technical Specifications

Part Number:	DHIP162U3B02C
--------------	---------------

Product Overview

Suitable Applications:	Indoor
------------------------	--------

Construction

Fiber Cable Construction

Fiber Type	Fiber Count	Subunit Color	Subunit Color 2
OM3	2	Aqua	Aqua

Fiber Color Coding:	White
---------------------	-------

Buffer Specification

Buffer Material	Buffer Diameter
PVC	900 µm

Bulk Cable Weight:	73 lbs/1000ft
--------------------	---------------

SubUnit Specifications

Fibers Per Subunit:	1
SubUnit Diameter:	0.118 in (3.0 mm)

Jacket Specifications

Total Number of Pairs:	2
Outer Jacket Color:	Apple Green
Number of Outer Jacket Ripcords:	1

Optical Characteristics

Fiber Core Diameter:	50/125µm
Max Attenuation at 1300 nm:	1.0 dB/km
Max Attenuation at 850 nm:	3.0 dB/km

Mechanical Characteristics

Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	20x Cable OD
Cable Min. Bend Radius Operation (Long Term)	10x Cable OD
Cable Max. Tensile Strength Installation (Short Term)	135 N (600 lbf)
Cable Max. Tensile Strength Operation (Long Term)	40 N (180 lbf)

Temperature Range

Operating Temp Range:	0C to +70C
Installation Temp Range:	0C to +60C
Storage Temp Range:	-40C to +70C

Standards

UL Rating/Flame Test:	Plenum
NEC/(UL) Specification:	CMP-OF
Telecommunications Standards:	ICEA S-120-742
REACH:	Complies
RoHS:	Complies

History

Update and Revision:	Revision Number: 0.15 Revision Date: 08-20-2019
----------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.