



Product: [CX3C0](#) 

COAX 3 FOAM FB20 PE CATV



Product Description

COAX 3 FOAM FB20 PE CATV

Technical Specifications

Product Overview

Suitable Applications:	Coaxial cables used in cabled distribution networks designed according the European Standard EN 50117; Operating at frequencies between 5 MHz and 2150 MHz; The International Standard IEC 1196
------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	Diameter +/- Tolerance	No. of Coax
8	Solid	BC - Bare Copper	3.38 mm	0.03 mm	1

Conductor Count:	1
------------------	---

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Dielectric	PE - Polyethylene (Foam)	14.9 mm	0.4 mm

Table Notes:	Centricity min. 85%
--------------	---------------------

Outer Shield Material

Type	Layer	Material	Coverage [%]	Min. Overlap	Nominal Diameter	Diameter +/- Tolerance	Coverage +/- Tolerance
Tape	1	Bare Copper (BC)	55%	5 mm			
Braid	2	Bare Copper (BC)	55%		15.8 mm	0.4 mm	5%

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene	19.8 mm	0.4 mm

Table Notes:	According to European Standard EN 50290-2-20
--------------	----------------------------------------------

Construction and Dimensions

Min Elongation at Breakof Jacket:	300 %
Min Tensile Strength of Jacket:	10 MPa

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. Conductor Loop	Max. Shield DCR
1.9 Ohm/km	4.5 Ohm/1000ft	2.6 Ohm/km

Capacitance

Nom. Capacitance	Capacitance Tolerance
54 pF/m	2 pF/m

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance	Regularity of Impedance
----------------------------------	----------------------------------	-------------------------

75 Ohm	3 Ohm	Min. 46 dB
--------	-------	------------

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	0.4 dB/100m
50 MHz	1.3 dB/100m
100 MHz	1.8 dB/100m
200 MHz	2.6 dB/100m
400 MHz	3.9 dB/100m
600 MHz	4.8 dB/100m
800 MHz	5.7 dB/100m
862 MHz	5.9 dB/100m
1000 MHz	6.5 dB/100m
1350 MHz	7.7 dB/100m
1750 MHz	9 dB/100m
2150 MHz	10.2 dB/100m
2400 MHz	10.9 dB/100m

Table Notes:	Max. attenuation 10% higher
--------------	-----------------------------

Delay

Nominal Velocity of Propagation (VP) [%]	Velocity of Propagation Tolerance
84%	2%

High Freq

Frequency [MHz]	Min. RL (Return Loss) [dB]
5 - 30 MHz	26 dB
30 - 470 MHz	26 dB
470 - 862 MHz	23 dB
862 - 2400 MHz	18 dB

Table Notes:	In each frequency band, 3 peak values up to 4 dB lower are allowed
--------------	--------------------------------------------------------------------

Screening

Frequency [MHz]	Min. Screening Attenuation
30 - 1000 MHz	95 dB

Screening Class:	A+
------------------	----

Transfer Impedance

Transfer Impedance
Max. 2.5 mOhm/m
Typ. 1.1 mOhm/m

Voltage

Voltage Test Dielectric
3.0 kV DC

Temperature Range

Installation Temp Range:	-5°C To +50°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-40°C To +70°C

Mechanical Characteristics

Bulk Cable Weight:	312 kg/km
Max. Pull Tension:	1200 N
Min Bend Radius (W/o Pulling Strength):	200 mm
Crush Resistance:	Max. 1% (load of 700N) N
Adhesion Dielectric:	53-530 N at 50 mm N

Standards

IEC Compliance:	IEC 1196
CENELEC Compliance:	EN 50117 and EN 50117-1
Series Type:	CATV-Trunk Type

Applicable Environmental and Other Programs

Environmental Space:	Outdoor
EU RoHS Compliance Date (yyyy-mm-dd):	1998-01-01

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
CX3C0.00700	Black	Reel	700 m	8719605047434
CX3C0.001050	Black	Reel	1,050 m	8719605047410
CX3C0.01700	Green	Reel	700 m	8719605047465
CX3C0.011050	Green	Reel	1,050 m	8719605047458

History

Update and Revision:	Revision Number: 0.172 Revision Date: 09-30-2020
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.