


**Part Number: CX4C2**

**COAX 4 FOAM FB14 FRNC/LSZH CATV**



**Product Description**

COAX 4 FOAM FB14 FRNC/LSZH CATV

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor - Euroclass Eca
Suitable Applications:	Coaxial cables used in cabled distribution networks designed according to the European Standard EN 50117; Operating at frequencies between 5 MHz and 2150 MHz; The International Standard IEC 1196

**Physical Characteristics (Overall)**

**Conductor**

Stranding	Material	Nominal Diameter	Diameter +/- Tolerance	No. of Coax
Solid	BC - Bare Copper	2.23 mm	0.03 mm	1

Conductor Count:	1
Conductor Size:	12 AWG

**Insulation**

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Dielectric	FPE - Foamed Polyethylene	10.2 mm	0.2 mm

Insulation, Table Note:	Centricity min. 85%
-------------------------	---------------------

**Outer Shield Material**

Type	Layer	Material	Coverage [%]	Min. Overlap	Nominal Diameter	Diameter +/- Tolerance	Coverage +/- Tolerance
Tape	1	Copper		4 mm			
Braid	2	BC - Bare Copper	59 %		11 mm	0.3 mm	5 %

**Outer Jacket Material**

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH / FRNC	13.8 mm	0.3 mm

OuterJacket1, Table Note:	According to European Standard HD 624
---------------------------	---------------------------------------

**Construction and Dimensions**

Min Elongation at Breakof Jacket:	125 %
Min Tensile Strength of Jacket:	9 MPa

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR	Max. Conductor Loop	Max. Shield DCR
4.5 Ohm/km	9 Ohm/1000ft	4.5 Ohm/km

**Capacitance**

Nom. Capacitance	Capacitance Tolerance
54 pF/m	2 pF/m

## Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance	Regularity of Impedance
75 Ohm	3 Ohm	Min. 46 dB

## High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	0.6 dB/100m
50 MHz	1.9 dB/100m
100 MHz	2.8 dB/100m
200 MHz	4 dB/100m
400 MHz	5.9 dB/100m
600 MHz	7.4 dB/100m
800 MHz	8.8 dB/100m
1000 MHz	10 dB/100m
1350 MHz	11.9 dB/100m
1750 MHz	13.9 dB/100m
2150 MHz	15.7 dB/100m
2400 MHz	16.8 dB/100m

## Delay

Nominal Velocity of Propagation (VP) [%]	Velocity of Propagation Tolerance
82 %	2 %

## High Freq

Frequency [MHz]	Min. RL (Return Loss) [dB]
5 - 30 MHz	26 dB
30 - 470 MHz	26 dB
470 - 862 MHz	23 dB
862 - 2400 MHz	18 dB

High Freq Table Note: In each frequency band, 3 peak values up to 4 dB lower are allowed

## Screening

Frequency [MHz]	Min. Screening Attenuation
30 - 1000 MHz	95 dB

Screening Class: A+

## Transfer Impedance

Transfer Impedance
Max. 2.5 mOhm/m
Typ. 1.9 mOhm/m

## Voltage

Voltage Test Dielectric
3.0 kV DC

## Temperature Range

Installation Temp Range:	-5°C To +50°C
Storage Temp Range:	-25°C To +70°C
Operating Temp Range:	-25°C To +70°C

## Mechanical Characteristics

Bulk Cable Weight:	196 kg/km
Max Recommended Pulling Tension:	400 N
Min Bend Radius (W/o Pulling Strength):	150 mm
Crush Resistance:	Max. 1% (load of 700N) N
Adhesion Dielectric:	35-350 N at 50 mm N

## Standards

ISO/IEC Compliance:	IEC 1196
CPR Euroclass:	Eca
GENELEC Compliance:	EN 50117 and EN 50117-1

Series Type:	CATV-Trunk Type
--------------	-----------------

## Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	1998-01-01
---------------------------------------	------------

## Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-24
LOI of Jacket:	Min. 35 %
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

## Part Number

### Variants

Item #	Color	Length
CX4C2.001000	Gray	1,000 m
CX4C2.00500	Gray	500 m
CX4C2.009999	Gray	1,000 m

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.