



Product: [CX9D0](#) 

COAX 9 DUOBONDPLUS PVC



Product Description

COAX [1.1/4.8] CX9D0 DUOBONDPLUS PVC CATV

Technical Specifications

Product Overview

Suitable Applications:	Coaxial cables used in cabled distribution networks designed according to the European Standard EN 50117 operating at frequencies between 5 MHz and 2150 MHz and the international standard IEC 1196
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Nominal Diameter	Diameter +/- Tolerance	No. of Coax
18	Solid	1.1 mm	0.02 mm	1

Conductor Count:	1
------------------	---

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Dielectric	PE - Polyethylene (Foam)	4.8 mm	0.15 mm

Table Notes:	Gas Injected
--------------	--------------

Outer Shield Material

Type	Layer	Material	Coverage [%]	Min. Overlap	Nominal Diameter	Diameter +/- Tolerance	Coverage +/- Tolerance
Tape	1	Tri-Laminate (Alum+Poly+Alum)	70%	1 mm			
Braid	2	Tinned Copper (TC)	70%				5%
Tape	3	Bi-Laminate (Alum+Poly)		1 mm	5.6 mm	0.2 mm	

Table Notes:	Foil Tape has L-Fold
--------------	----------------------

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
PVC - Polyvinyl Chloride	7.1 mm	0.2 mm

Table Notes:	According to European Standard EN 50290-2-20
--------------	--

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. Conductor Loop	Outer Conductor DCR
19 Ohm/km	33 Ohm/km	14 Ohm/km

Capacitance

Nom. Capacitance	Capacitance Tolerance
51 pF/m	2 pF/m

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance	Regularity of Impedance
75 Ohm	3 Ohm	40 dB

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
30-470 MHz	27 dB
470-1000 MHz	24 dB
1000-2000 MHz	18 dB
2000-3000 MHz	16 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	1.5 dB/100m
50 MHz	4.0 dB/100m
100 MHz	5.7 dB/100m
200 MHz	8.2 dB/100m
400 MHz	11.8 dB/100m
600 MHz	14.7 dB/100m
800 MHz	17.2 dB/100m
1000 MHz	19.4 dB/100m
1350 MHz	23.0 dB/100m
1750 MHz	27.0 dB/100m
2000 MHz	28.7 dB/100m
2150 MHz	30.0 dB/100m
2400 MHz	32.0 dB/100m
3000 MHz	36.0 dB/100m

Delay

Nominal Velocity of Propagation (VP) [%]	Velocity of Propagation Tolerance
86%	2%

Table Notes: Maximum attenuation is 10% higher

Screening

Frequency [MHz]	Min. Screening Attenuation
30-1000 MHz	95 dB
1000-2000 MHz	85 dB
2000-3000 MHz	75 dB

Screening Class: A+

Transfer Impedance

Frequency [MHz]	Transfer Impedance
5-30 MHz	max. 2.5 mOhm/m

Voltage

Voltage Test Dielectric
2.0 kV DC

Temperature Range

Installation Temp Rating:	-5 °C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-40°C To +70°C

Mechanical Characteristics

Max. Pull Tension:	60 N
Min Bend Radius (W/o Pulling Strength):	35 mm
Max Crush Resistance (Load of 700N):	1 %

Standards

CPR Euroclass:	Eca
CENELEC Compliance:	EN 50117-1

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Eca
----------------------	------------------------

EU RoHS Compliance Date (yyyy-mm-dd):	2015-01-07
---------------------------------------	------------

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
-------------------	---------------

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
CX9D0.01B100	Black	Flat Box	100 m	8719605123008
CX9D0.01U250	Black	UnReel	250 m	8719605123015
CX9D0.01500	Black	Reel	500 m	8719605123022
CX9D0.00B100	White	Flat Box	100 m	8719605048196
CX9D0.00250	White	Reel	250 m	8719605048172
CX9D0.00U250	White	UnReel	250 m	8719605048202
CX9D0.00500	White	Reel	500 m	8719605048189

History

Update and Revision:	Revision Number: 0.82 Revision Date: 09-30-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.