



Product: [DKAG50MA024BEAA](#)

OM2, MLT, Dry Core, FRP Armored, double PE & Nylon Jacket OFC

Product Description

OM2, MLT, Dry Core –Inner HDPE & Nylon Sheath, Flat FRP Armored, Outer HDPE & Nylon Sheath, All Dielectric Optical Fiber Cable, Termite & Rodent Resistant

Technical Specifications

Product Overview

Suitable Applications:	For outdoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor use in networks for industrial, telecom, cable TV and/or broadcast. Easy to install in ducts, tunnels and trenches and/or tubes. Suitable for Direct Burial.
------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OM2	24

Fiber Color Coding:	TIA coding (Gxxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua
---------------------	---------------------------------------------------------------------------------------------------------

Buffer Specification

Buffer Material
Buffer Tube Material:Thermoplastic Material (PBT), Buffer Tube Filling Material: Synthetic Thixotropic Gel

Cable Core Waterblocking:	Waterblocking Yarns + Tape
Bulk Cable Weight:	167 kg/km

Inner Jacket

Material:	PE - Polyethylene
Material@InnerJacket2:	Nylon

Outer Jacket Specifications

Outer Jacket

Material
PE - Polyethylene
Nylon

Table Notes:	Armor Type: Flat Fiber Reinforced Plastic Rod Cable Overall Diameter: 13.5mm
--------------	------------------------------------------------------------------------------

Optical Characteristics

Max. Attenuation at 1300 nm:	1.0 dB/km
Max. Attenuation at 850 nm:	3.0 dB/km

Mechanical Characteristics

Mechanical Tests

Description	Tested Standard	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E11	30 x OD
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	15 x OD
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	4000 N (899 lbf)

Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	1200 N (270 lbf)
---------------------------------------------------	-------------------	------------------

Temperature Range

Operating Temperature Range:	- 30 To + 70
Installation Temperature Range:	- 10 To + 60
Storage Temperature Range:	- 40 To + 70

Standards

ISO/IEC Compliance:	ISO/IEC 11801
---------------------	---------------

Product Notes

Notes:	Jacket: Inner HDPE & Nylon sheath(black), Outer HDPE & Nylon sheath (blue), Armor Type and Material: Flat Fiber Reinforced Plastic Rod, Maximum Crush Resistance for Short Term: 4000N/100mm, Duration: 1min, Maximum Crush Resistance for Long Term: 2000N/100mm, Duration: 10min
--------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.20 Revision Date: 04-15-2025
----------------------	-------------------------------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.