



Product: [DAS6P](#)

Distributed Antenna System RG6 Type BC Coax, CMP

Product Description

DAS RG-6 type, 18 AWG solid .040" bare copper conductor, foamed FEP insulation, Duobond® II foil shield + tinned copper braid shield (85% coverage), CMP rated, low smoke PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	Distributed Antenna System
------------------------	----------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BC - Bare Copper	0.040 in	1

Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.168 in

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
Braid	2	Tinned Copper (TC)		85%

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.233 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
6.4 Ohm/1000ft	3.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.1 pF/ft

Inductance

Nominal Inductance
0.103 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5 - 3000 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	0.55 dB/100ft
10 MHz	0.75 dB/100ft
50 MHz	1.50 dB/100ft
100 MHz	2.10 dB/100ft
200 MHz	3.00 dB/100ft
400 MHz	4.30 dB/100ft
700 MHz	6.00 dB/100ft
900 MHz	6.90 dB/100ft
1000 MHz	7.30 dB/100ft
1500 MHz	9.20 dB/100ft
2000 MHz	10.90 dB/100ft
2250 MHz	11.60 dB/100ft
3000 MHz	13.70 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.24 ns/ft	82%

Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	Return Loss: Fixed bridge and termination
-----------------------------------	---

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-35°C To +75°C

Mechanical Characteristics

UV Resistance:	No
Bulk Cable Weight:	34 lbs/1000ft
Max. Pull Tension:	59 lbs
Min. Bend Radius/Minor Axis:	2.3 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
RG Type:	6

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	DAS11R
--------------------	--------

Variants

Item #	Color	Put-Up Type	Length	UPC
DAS6P 0101000	Black	Reel	1,000 ft	612825285120
DAS6P 0103000	Black	Reel	3,000 ft	612825285137

History

Update and Revision:	Revision Number: 0.74 Revision Date: 09-10-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.