


Part Number: DB6PL2-25



Double Bubble RG-6 Plenum "F" Coax Compression Connector

Product Description

Double Bubble RG6 "F" Plenum connector, fits most plenum RG6 coaxial cables. Compression design that molds the metal completely around the cable.

Technical Specifications

Product Overview

Suitable Applications:	CCTV, Security Cameras, Video
------------------------	-------------------------------

Physical Characteristics (Overall)

Conductor Size:	18 AWG
Packaging:	25 Pack
Number of Pieces:	1

Connectors

Materials

Material
Nickel plated Brass

Electrical Characteristics

Impedance

Nominal Characteristic Impedance
75 Ohms

Return Loss (RL)

Frequency [MHz]
DC-1 GHz 31 dB Return Loss 1.05 VSWR
DC-2 GHz 26 dB Return Loss 1.09 VSWR
DC-3 GHz 21 dB Return Loss 1.18 VSWR

Mechanical Characteristics

Footprint/Type:	Coax
Connector Interface Type:	F
Gender:	Male - plug
Connector Series Name:	Double Bubble
Locking:	No
Tool Compatibility:	CPLCRBC-BR (compression), PS59/6/RGB (strip)
Termination Type:	Compression
Cable Center Conductor Diameter Limits:	.0399 - .0418 inch
Cable Dielectric Diameter Limits:	.165 - .172 inch
Cable Outer Jacket Diameter Limits:	.220 - .250 inch

Standards

RG Type:	6/U Type
----------	----------

Series Type: 6/U

Applicable Environmental and Other Programs

EU CE Mark: Yes

Suitability

Suitability - Indoor: Yes

Part Number

Variants

Item #	Color	UPC
DB6PL2-25	No Color	845671000405

Patent: <https://www.belden.com/resources/patents>

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.