



Product: [E601 Cordsets](#) 

Cord Sets, DataTuff® Cat 6 IP20 RJ45 Cord Set

Product Description

Cat 6 IP20 RJ45 cord set, unshielded with solid conductors (Belden cable 7940A)

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material
24	Solid	BC - Bare Copper

Conductor Size:	24 AWG
Total Number of Pairs:	4

Insulation

Material
PO - Polyolefin

Outer Shield

Material
No Shield

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color	Type
Plug	Polycarbonate	Black	RJ45
Boot	UL94V-0 flame retardant		
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating		

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	2.500 in.
----------------------------------	-----------

Termination Interface

Connection	Durabilities
Mated Connection	750 Cycles

Standards

NEC/(UL) Compliance:	CMR, CMX-Outdoor
UL Rating:	Riser
CSA Rating:	FT4
TIA/EIA Compliance:	Category 6 - TIA 568-C.2, Class E - ISO/IEC 11801:2002 Ed.2 Amendment 4
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MIL Order #39 (China RoHS):	EUP 50

Flammability, LSOH, Toxicity Testing

UL voltage rating:	300 V RMS
Safety Listing:	c(UL)us Listed

Related Part Numbers

Variants

Item #	Color
E601010 010S1	Black

Product Notes

Notes:	US Patent #s 5, 606, 151; 5, 734, 126. Ethernet/IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc., , IEC 60603-7
Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length.

History

Update and Revision:	Revision Number: 0.189 Revision Date: 07-10-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.