



**Product:** [DLC224](#)

DMX Lighting Cable, 4 Cond, 24 AWG Stranded TC

### Product Description

Gepco a Belden Brand, Flexible DMX512 Lighting Control Cable, 4 Conductor 24 AWG (7x32) stranded tinned copper, Foam PE insulation, foil shield plus 90% TC braid with 24 AWG stranded TC drain wire, all weather TPE jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	RS-485, DMX-512
------------------------	-----------------

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Conductors
24	7x32	TC - Tinned Copper	4

Conductor Count:	4
------------------	---

##### Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.022 in

##### Color Chart

Number	Color
1	Black
2	White
3	Red
4	Blue

##### Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	24
Braid		Tinned Copper (TC)		90%		

##### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	0.27 in	0.042 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
24 Ohm/1000ft	2.2 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
10.4 pF/ft	18.7 pF/ft

##### Impedance

**Nominal Characteristic Impedance**

120 Ohm

**High Frequency (Nominal/Typical)**

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100m

**Delay**

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66%

**Current****Max. Recommended Current [A]**

2.1 Amps per Conductor at 25°C

**Voltage****UL Voltage Rating**

300 V RMS

**Temperature Range**

UL Temp Rating:	80°C
Operating Temperature Range:	-30°C To +80°C

**Mechanical Characteristics**

Bulk Cable Weight:	49 lbs/1000ft
Max. Pull Tension:	87 lbs
Min. Bend Radius/Minor Axis:	2.7 in

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

**Suitability**

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Related Part Numbers****Variants**

Item #	Color	Put-Up Type	Length	UPC
DLC224.99	Black	Reel		612825406341
DLC224.41	Black	Reel	1,000 ft	612825391241

**History**

Update and Revision:	Revision Number: 0.133 Revision Date: 12-20-2022
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and

regulations based on their individual usage of the product.