



Product: [DOSP6AU](#)

Category 6A OSP Cable, 4 Pair, U/UTP, Gel Free

Product Description

Category 6A Premise Horizontal Cable, OSP Rated, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Gel Free

Technical Specifications

Product Overview

Suitable Applications:	OSP-Outside Plant, Premise Horizontal Cable, Ethernet up to 10GBASE-T, Wi-Fi 6, Wi-Fi 5, PoE++, PoE+, PoE, Noisy Environments, HDBaseT, IP Cameras
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White & Blue, White & Orange, White & Green, White & Brown

Outer Jacket

Separator	Material	Nom. Diameter	Ripcord
Center Member (Patented T-Spline®), EquiBlock™ Barrier Technology	PO - Polyolefin	0.29 in (7.4 mm)	Yes

Overall Cable Diameter (Nominal):	0.29 in (7.4 mm)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
82 Ohm/km (25 Ohm/1000ft)	45 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	68%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT [dB]	Min. PSAACRF [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.1	74.3	72.3	72.2	70.2	67.8	64.8	20.0	105 +/- 10	115 +/- 15	67.0	67.0	40.0	35.0
4	3.8	65.3	63.3	61.5	59.5	55.8	52.8	23.0	105 +/- 10	100 +/- 7	67.0	66.2	40.0	23.0
8	5.3	60.8	58.8	55.4	53.4	49.7	46.7	24.5	100 +/- 22	100 +/- 7	67.0	60.1	40.0	16.9
10	5.9	59.3	57.3	53.4	51.4	47.8	44.8	25.0	100 +/- 22	100 +/- 7	67.0	58.2	40.0	15.0
16	7.5	56.2	54.2	48.8	46.8	43.7	40.7	25.0	100 +/- 22	100 +/- 7	67.0	54.1	38.0	10.9
20	8.4	54.8	52.8	46.4	44.4	41.8	38.8	25.0	100 +/- 22	100 +/- 7	67.0	52.2	37.0	9.0
25	9.4	53.3	51.3	44.0	42.0	39.8	36.8	24.3	100 +/- 22	100 +/- 7	67.0	50.2	36.0	7.0

31.25	10.5	51.9	49.9	41.4	39.4	37.9	34.9	23.6	100 +/- 22	100 +/- 7	67.0	48.3	35.1	5.1
62.5	15.0	47.4	45.4	32.4	30.4	31.9	28.9	21.5	100 +/- 22	100 +/- 7	65.6	42.3	32.0	
100	19.1	44.3	42.3	25.2	23.2	27.8	24.8	20.1	100 +/- 22	100 +/- 7	62.5	38.2	30.0	
200	27.6	39.8	37.8	12.2	10.2	21.8	18.8	18.0	100 +/- 22	100 +/- 7	58.0	32.2	27.0	
250	31.1	38.3	36.3	7.3	5.3	19.8	16.8	17.3	100 +/- 32	100 +/- 7	56.5	30.2	26.0	
300	34.3	37.1	35.1	2.9	0.9	18.3	15.3	16.8	100 +/- 32	100 +/- 7	55.3	28.7	25.2	
350	37.2	36.1	34.1			16.9	13.9	16.3	100 +/- 32	100 +/- 7	54.3	27.3	24.6	
400	40.1	35.3	33.3			15.8	12.8	15.9	100 +/- 32	100 +/- 7	53.5	26.2	24.0	
450	42.7	34.5	32.5			14.7	11.7	15.5	100 +/- 32	100 +/- 7	52.7	25.1	23.5	
500	45.3	33.8	31.8			13.8	10.8	15.2	100 +/- 32	100 +/- 7	52.0	24.2	23.0	

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-20°C To +70°C	0°C To +60°C	-40°C To +75°C

Bend Radius

Installation Min.
2.9 in (74 mm)

Max. Pull Tension: 25 lbs (11 kg)

Bulk Cable Weight: 33 lbs/1000ft (49 kg/km)

Standards and Compliance

Environmental Suitability:	Outdoor - Water Exposure, Outdoor
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class EA
CENELEC Compliance:	Segregation class according EN50174-2 = a

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0. Not Suitable for Direct Burial. Cable jacket system is specially designed to protect cable core. Cable contains no water-blocking tapes, gels, or powders. Install in accordance with all applicable electrical codes. Maintain jacket integrity throughout installation process. Do not allow water or fluids to penetrate jacket sheath or to enter ends of cable. Ensure ends of cable will be protected from water/fluids after installation. Belden recommends using an entrance demarcation point when transitioning inside buildings with OSP cables. The suggested transition point is the REVConnect core coupler, part number RVACPUBK-S1.
--------	--

History

Update and Revision:	Revision Number: 0.62 Revision Date: 04-29-2024
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length
DOSP6AU 0101000	Black	Reel	1,000 ft

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.