



Product: [ECX-4U-INSTR](#)

FX ECX 4U Internal Strain Relief

Product Description

ECX-4U-INSTR contains 1 internal strain relief. This component is used to secure distribution cables to a FX ECX 4U Patch Panel Housing.

Technical Specifications

Product Overview

| | |
|------------------------|-----------------------------------|
| Environmental Space: | Indoor |
| Suitable Applications: | ECX Patch Panel, cable management |

Construction

| | |
|---------|-----------|
| Weight: | 0.100 lbs |
| Height: | 0.750 in |
| Width: | 2.750 in |
| Depth: | 2.000 in |

Temperature Range

| | |
|--------------------------|----------------|
| Installation Temp Range: | -10°C To +60°C |
| Storage Temp Range: | -40°C To +70°C |

Product Material

Materials

| Description | Material | Color |
|------------------------|----------|-------|
| Internal strain relief | Plastic | Black |

Standards

| | |
|---------------------------------------|------------|
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU RoHS Compliance Date (yyyy-mm-dd): | 2013-01-01 |
| UV/ Sunlight Protection: | Yes |

Part Number

| | |
|----------------|--------------------|
| Related Parts: | ECX Patch Panel 4U |
|----------------|--------------------|

Variants

| Item # | Color | UPC |
|--------------|-------|--------------|
| ECX-4U-INSTR | Black | 611589224550 |

Product Notes

| | |
|------------|--------------------------------|
| Packaging: | Parts packaged in a bubble bag |
|------------|--------------------------------|

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.37 Revision Date: 01-31-2020 |
|----------------------|---|

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.