

Product: [FAN UNIT W/O CORD E-SERIES](#) 



Fan unit with thermostat for E-Series Cabinets and wallmounts

Product Description

Fan unit with thermostat, without power cord (C14 Power socket for 230V) for E-Series Cabinets and wallmounts. Unit with 1 fan (airflow 160m3/h), 2 fans (airflow 320 m3/h), 3 fans (airflow 480 m3/h), 4 fans (airflow 640 m3/h), 6 fans (airflow 960 m3/h)

Technical Specifications

Application

Suitable Applications:	Ventilating hot air from the cabinets via the top or Blowing Cold air from the bottom into the cabinets.
Environmental Space:	Indoor

Standards

EU Directive 2011/65/EU (ROHS II):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2016-04-04
MII Order #39 (China RoHS):	EUP 50

Part Number

Included Parts:	Package does not include power cord. For C13 power grid, cord sets are available: CSC13C14yyBK (yy=24, 36 or 48 inch)
Packaging:	Individually packed in a box.

Variants

Item #	Color	Number of Fans	Application
EDAF1121	Gray	2	Free standing E-Series Cabinets (except ESN 600mm depth)
EDAF1122	Black	2	Free standing E-Series Cabinets (except ESN 600mm depth)
EDAF1141	Gray	4	Free standing E-Series Cabinets (except ESN 600mm depth)
EDAF1142	Black	4	Free standing E-Series Cabinets (except ESN 600mm depth)
EDAF1161	Gray	6	Free standing E-Series Cabinets (except ESN 600mm depth)
EDAF1162	Black	6	Free standing E-Series Cabinets (except ESN 600mm depth)
EDAF6111	Gray	1	ESN 600mm depth Cabinet and Wall-Mount E-Series
EDAF6112	Black	1	ESN 600mm depth Cabinet and Wall-Mount E-Series
EDAF6121	Gray	2	ESN 600mm depth Cabinet and Wall-Mount E-Series
EDAF6122	Black	2	ESN 600mm depth Cabinet and Wall-Mount E-Series
EDAF6131	Gray	3	ESN 600mm depth Cabinet and Wall-Mount E-Series
EDAF6132	Black	3	ESN 600mm depth Cabinet and Wall-Mount E-Series

Update and Revision:	Revision Number: 0.46 Revision Date: 11-09-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.