




Product: [FC3F04LD4F4A](#)



FX XHD FANOUT OM3 04P MPO12(F)/8F LC_DX SR4 AQ_ID

Product Description

FANOUT OM3 04P MPO12(F) - 8F_LC/PC DUPLEX WITH PULL TAB CONNECTOR SR4, AQUA

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Data Center, LAN, Equipment Room, Telecommunication room, Workstation Area

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OM3	8

Length:	200 mm
---------	--------

Optical Characteristics

Fiber Core Diameter:	50/125 μ m
----------------------	----------------

Mechanical Characteristics

Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	15x Cable OD
Cable Min. Bend Radius Operation (Long Term)	10x Cable OD

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-10°C To +60°C

Product Material

Materials

Description	Material	Color	Type
Connectors for end 1	Plastic	Aqua	MPO-12 Female
Connectors for end 2	Plastic	Aqua	LC Duplex Pull tab
Boots for end 1	Rubber	Black	
Boots for end 2	Rubber	White	900 μ m Mini boot
Ferrules for end 2	Zirconia-Ceramic		1.25 mm
Jacket	OFN		900 μ m Tight buffer, Heat shrink transition

Transmission-Characteristics

Polarity Identification:	SR4
--------------------------	-----

Fiber Connector Performance

Description	Connector Type	Max. Insertion Loss	Min. Return Loss
-------------	----------------	---------------------	------------------

Connectors for end 1	MPO-12 Female	0.35 dB	-25 dB
Connectors for end 2	LC Duplex	0.25 dB	-25 dB

Standards

TIA/EIA Compliance:	TIA 568-3
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50
Safety Listing:	ACMA

Product Notes

Packaging:	Individually packaged in a plastic bag
Notes:	Velcro (1in long), ID color labels and Dust caps are included

History

Update and Revision:	Revision Number: 0.29 Revision Date: 04-28-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.