


Product: [EAGLE40-6TX-EECC-HV-UN](#) 



Next-Generation, Industrial Train Firewall with Enhanced Cybersecurity Including Support for Intrusion Detection Systems (IDS) and Deep Packet Inspection (DPI)

Product Description

The Hirschmann EAGLE40-6M is a next-generation firewall designed for use on-board in railway rolling stock applications with six (6) 2.5-Gigabit Ethernet M12 X-coded ports, real-time traffic monitoring, advanced threat protection, and secure remote connectivity using IPSec VPN. Includes deep packet inspection (DPI) modules.

Technical Specifications

Product description

Part Number:	942300302
Port type and quantity:	6 x GbE X-coded M12 ports
Port Speed:	2.5 Gbit/s X-coded M12

Displays

LEDs:	Power Supply Status LED, Device Status LED, HDD Activity LED, Port Status LEDs
-------	--

More Interfaces

USB interface:	1 x USB 2.0/3.0, 5-pin A-coded M12
Serial Interface:	1 x Serial Console Port (4-pin, A-coded M12)
Power Supply:	1 x 5 pin K-coded M12

Hardware

CPU:	Intel® Core™ Apollo Lake-I x7-E3950 @ 1.6 GHz
Memory:	8GB DDR3
Storage:	64GB SSD

Power requirements

Operating Voltage:	Dual 24 V DC - 110 V DC
Power consumption:	25 W

Security features

Multipoint VPN:	IPSec, IKE v1/v2, 3DES, AES (-128, -192, -256), Pre-Shared Key (PSK), X.509v3 Certificates, MD5, SHA-1, NAT-T, Hub-and-Spoke
Deep Packet Inspection:	Unified Protection Suite (All Enforcers)
Stateful inspection firewall:	Firewall rules (incoming/outgoing, management)

Software

Redundancy:	VRRP (Virtual Router Redundancy Protocol), Tracking Framework for VRRP
Management:	SNMPv3, SSH2/SFTP/SCP, HTTPS, Serial CLI, SNMPv1/2, local and central User Management (RADIUS), HiDiscovery, Industrial HiVision, HiView, LLDP
Diagnostics:	LEDs (Power, Link Status, Data, Status), Log File, Syslog, Configuration check, RMON (statistics), Trap for changes and configuration saves
Configuration:	Command Line Interface (CLI), Web Interface, Auto-Configuration Adapter (ACA22), HiDiscovery, Industrial HiVision, HiView
Security:	DoS prevention, IPSec VPN, Audit trail, Role-based Access Control, Remote Authentication via RADIUS, IEEE 1686 compliant configuration possible, Firewall Learning Mode, Routed Firewall Mode and Transparent Firewall Mode for Layer 3 and Layer 2 packet filtering rules, Management VLAN, Ingress storm protection, Authentication using LDAP, Deep Packet Inspection (DPI) Enforcer Modules: Modbus TCP, OPC, EtherNet/IP, IEC104, DNP3, and AMP; Support for CylusOne IDS (Docker)
Miscellaneous:	NTP Client and Server, DHCP L3 Relay

Routing:	VLAN and port based routing, static routing, static multicast, IGMP query, multinetting, IP masquerading, 1-to-1 NAT, port forwarding, Static and Dynamic ARP entries, OSPFv2, Static route tracking
----------	--

Ambient conditions

MTBF (Telecordia SR-332 Issue 4) @ 25°C:	GB 25°C: 842,752 h / GB 75°C: 168,169 h
Operating temperature:	-40 –+70 °C
Storage temperature (up to 3 months):	-40 °C to +85 °C
Storage temperature (up to 1 year):	-40°C to +70 °C
Storage temperature (up to 2 years):	-40°C to +50 °C
Storage temperature (up to 10 years):	0°C to +30 °C
Protective paint on PCB:	Yes (conformal coating)

Mechanical construction

Dimensions (WxHxD):	305 x 83 x 180 (mm)
Weight:	4.2 kg
Housing Material:	Aluminum Extrusion Top cover, Others by using SGCC
Mounting:	Wall mounting
Protection class:	IP40

Approvals

Basis Standard:	CE, FCC
Safety of industrial control equipment:	UL 61010, EN 61131
Safety of information technology equipment:	IEC 62368-2
Railway norm:	EN 50155, EN 50121-4, EN 45545, EMV06

Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
------------	---

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com/index.html
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.22 Revision Date: 11-11-2024
----------------------	---

Variants

Item #	Type
942300302	EAGLE40-6TX-EECC-HV-UN

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.