



Product: [ECO-SMART6A](#)

Category 6A Unbonded – LSZH Jacket

Product Description

26 AWG solid bare copper conductors, non-plenum, Polyolefin insulation, twisted pairs, central spline, overall cabling PET tape, Separation tape, LSZH jacket.

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building backbone Cable. Support current and future category 6 and 6A applications: such as 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100Base-T, 10Base-T, ISDN, ATM as well as PoE application etc.
------------------------	---

Construction Details

Conductor

Size	Stranding	Stranding Class	Material	No. of Pairs	No. of Elements
26 AWG	Solid	Class 1	BC - Bare Copper	4	8

Insulation

Material	Nom. Insulation Diameter	Color Code
PO - Polyolefin	0.83 mm (0.033 in)	Blue & White with Blue Strip, Orange & White with Orange Strip, Green & White with Green Strip, Brown & White with Brown Strip

Table Notes: All Cores laid up together with Central Spline fillers & wrapped with Separator tape + PET Tape.

Outer Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

Overall Cable Diameter (Nominal): 5.7 mm (0.22 in)

Electrical Characteristics

Electricals

Max. Conductor DCR
148 Ohm/km @ 20 Deg. C

Table Notes: The utilization of 26 AWG conductor which does not meet the 24 to 22 AWG conductor size of horizontal cable in ANSI/TIA-568.2-D, resulting in increased attenuation which derates the maximum permanent link of the cable to 60 meters.

Delay

Max. Delay Skew	Nom. Velocity of Prop.
44 ns/60m	67%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]
1	1.9 dB/60m	65	62	64.2	61.2	19.1
4	3.5 dB/60m	64.1	61.8	52.1	49.1	21
8	5.0 dB/60m	59.4	57	46.1	43.1	21
10	5.5 dB/60m	57.8	55.5	44.2	41.2	21
16	7.0 dB/60m	54.6	52.2	40.1	37.1	20
20	7.8 dB/60m	53.1	50.7	38.2	35.2	19.5
25	8.8 dB/60m	51.5	49.1	36.2	33.2	19

31.25	9.8 dB/60m	50	47.5	34.3	31.3	18.5
100	18.8 dB/60m	41.8	39.3	24.2	21.1	14
200	26.1 dB/60m	36.9	34.3	18.2	15.2	11
250	29.5 dB/60m	35.3	32.7	16.2	13.2	10
300	32.7 dB/60m	34	31.4	14.6	11.6	9.2
400	38.4 dB/60m	29.9	27.1	12.1	9.1	8
500	43.8 dB/60m	26.7	23.8	10.2	7.2	8

Voltage

Voltage Rating	Breakdown Voltage
72 V DC	2.5 kV DC for 2 Sec.

Mechanical Characteristics

Temperature

Operating	Storage
-20°C to + 75°C	-20°C to + 60°C

Bend Radius

Installation Min.
45 mm (1.8 in)

Max. Pull Tension:	110 N (25 lbf)
Bulk Cable Weight:	30 kg/km (20 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	Indoor, Non-Halogenated
Flammability / Reaction to Fire:	IEC 60332-1-2
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	IEC 61156-5, ISO/IEC 11801
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.10 Revision Date: 11-14-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.