



**Product:** [ECX-01WH](#)

## FX ECX Single Cassette Holder

### Product Description

FX ECX Single Cassette Holder, Black Finish, Wall-mountable, DIN-Rail-Mountable with ECX-DINKIT Accessory

### Technical Specifications

#### Product Overview

Suitable Applications:	Backbone, Telecommunications Rooms and Closet, Main Distribution Room, Zone Cabling, Campus, Wall-Mount Enclosures, Electronics Cabinets
------------------------	------------------------------------------------------------------------------------------------------------------------------------------

#### Construction

Weight:	2.050 lbs
Height:	6.480 in
Length:	11.560 in
Depth:	1.875 in

#### Physical Specifications

Max Capacity:	1 ECX Cassette of 24 fibers (LC); 12 fibers (SC)
---------------	--------------------------------------------------

#### Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

#### Product Material

##### Materials

Description	Material	Color
Single Cassette Wall-Mount	Steel	Black

#### Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

#### Related Part Numbers

Included Parts:	ECX Single Cassette Holder; (8) Velcro Cable Ties; (4) Phillips Wood Screws; (1) ECX 3/6/12 Port Label; (1) ECX 4/8 Port Label; XBS-11-0001 Grounding Kit
Related Parts:	FX ECX DIN Rail Clip, FX Distribution Fiber Cable, FX Splice Pigtails, FX ECX Fiber Cassettes

#### Product Notes

Packaging:	Individually packaged in a cardboard box
Notes:	For more information, please refer to our web site at <a href="http://www.belden.com">http://www.belden.com</a> . Refer to document PX107209EF to see installation procedures.

#### History

Update and Revision:	Revision Number: 0.9 Revision Date: 08-22-2022
----------------------	------------------------------------------------

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.