



**Product:** [ECX Splitter Cassette 1x8](#)



**FX ECX Splitter Cassette, OS2, 1x8**

**Product Description**

FX ECX Splitter Cassette, OS2, 1x8, 4 Splitter, LC/APC Input, LC-SX/APC Output, Front

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Passive Optical LAN

**Construction**

**Fiber Cable Construction**

Fiber Type	
OS2	
Weight:	0.272 kg
Height:	33.020 mm
Width:	161.036 mm
Length:	221.996 mm

**Physical Specifications**

Max Capacity:	8 Fibers (Output)
---------------	-------------------

**Mechanical Characteristics**

Front Connection:	Static
Termination Style:	Front

**Temperature Range**

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-10°C To +60°C

**Product Material**

**Materials**

Description	Material	Color	Type
Housing	PC/ABS	Black	
Cover	Polycarbonate	Clear-Light Smoke	
Frame	PC/ABS	Black	Lead Frame
Adapter Output	Plastic - UL94V-0	Green	LC-Quad w/ Internal Shutters
Adapter Input	Plastic - UL94V-0	Green	LC-Quad w/ Internal Shutters

**Standards**

TIA/EIA Compliance:	Telcordia GR-1209-CORE (splitters only), Telcordia GR-1221-CORE (splitters only)
MII Order #39 (China RoHS):	EUP 50

**Related Part Numbers**

Related Parts:	FX ECX Housings (4U, 2U, 1U), ECX Splice Cassettes, Patch Cords
----------------	---

**Variants**

Item #
SCSX4108LLF

**Product Notes**

Packaging:	Individually packaged in a plastic shell. Shipped in cardboard box (12/box)
------------	---

**History**

Update and Revision:	Revision Number: 0.25 Revision Date: 05-31-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.