



Product: [FC3X06LKFMN](#)

FX ECX CASS OM3 06P MASS FUSION PIGTAIL LC KEYED DUPLEX



Product Description

FX ECX CASSETTE, OM3, 06 PORTS, WITH 250um MASS FUSION RIBBON PIGTAILS, LC KEYED DUPLEX, RED ADAPTERS

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Environmental Space: | Indoor |
| Suitable Applications: | FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers |

Construction

Fiber Cable Construction

| | |
|-------------------|----------|
| Fiber Type | |
| OM3 | |
| Height: | 1.300 in |
| Width: | 6.340 in |
| Length: | 8.740 in |

Physical Specifications

| | |
|---------------|------------------------------|
| Max Capacity: | 12 Fibers, 6 LC Duplex Ports |
|---------------|------------------------------|

Mechanical Characteristics

| | |
|-------------------|--------|
| Front Connection: | Static |
|-------------------|--------|

Temperature Range

| | |
|------------------------------|----------------|
| Operating Temperature Range: | -10°C To +60°C |
| Storage Temperature Range: | -10°C To +75°C |

Product Material

Materials

| Description | Material | Color |
|----------------------|-------------------|-------|
| Adapter Sleeve | Zirconia-Ceramic | |
| Front Connector Body | Plastic - UL94V-0 | Red |
| Cassette Assembly | Plastic - UL94V-0 | Black |

Transmission-Characteristics

Fiber Connector Performance

| | |
|----------------------------|-------------------------|
| Max. Insertion Loss | Min. Return Loss |
| 0.25 dB | -30 dB |

Standards

| | |
|-----------------------------------|--------|
| EU Directive 2011/65/EU (RoHS 2): | Yes |
| MII Order #39 (China RoHS): | EUP 50 |

Related Part Numbers

| | |
|-----------------|---|
| Included Parts: | 250um pigtails, splice sleeves and cable ties |
|-----------------|---|

Variants

| Item # | Connector Type | Port Count |
|--------------|-----------------|------------|
| FC3X06LKFMNA | LC Keyed Aqua | 6 Port |
| FC3X06LKFMNB | LC Keyed Blue | 6 Port |
| FC3X06LKFMNG | LC Keyed Green | 6 Port |
| FC3X06LKFMNM | LC Keyed Brown | 6 Port |
| FC3X06LKFMNN | LC Keyed Black | 6 Port |
| FC3X06LKFMNO | LC Keyed Orange | 6 Port |
| FC3X06LKFMNP | LC Keyed Rose | 6 Port |
| FC3X06LKFMNR | LC Keyed Red | 6 Port |
| FC3X06LKFMNS | LC Keyed Gray | 6 Port |
| FC3X06LKFMNV | LC Keyed Violet | 6 Port |
| FC3X06LKFMNW | LC Keyed White | 6 Port |
| FC3X06LKFMNY | LC Keyed Yellow | 6 Port |

Product Notes

| | |
|------------|--|
| Packaging: | Individually packaged in a plastic shell, shipped in cardboard box (12/box) |
| Notes: | Splice Holder is included. Splice holder is compatible with Belden Splice Sleeves part numbers (Post-Shrink Diameter): FXFUHS900AB25(2.5mm), FXFUHS9T2CB25 (2.0mm), FXFUHS250DB25 (1.5mm) and FXFUHSRIBEB12(Oval 4.1mmX4.6mm). |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.13 Revision Date: 12-13-2023 |
|----------------------|---|

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.