



**Product:** [FDCP001R9LBY](#)

FX Indoor/Outdoor, OS2 G.657.B3, Drop, 1 Fiber, OFNR, Lime Green Jacket, Reel-in-box - 450m

**Product Description**  
FX Indoor/Outdoor, OS2 G.657.B3, Drop, 1 Fiber, OFNR, Lime Green Jacket, Reel-in-box - 450m

**Technical Specifications**

**Product Overview**

Product Category:	Fiber Drop Cable
Suitable Applications:	Provides easy routing and 900 µm tight-buffered fiber supports fast and robust field terminations. Ideal for fiber-to-the-subscriber applications.

**Fiber Specifications**

Fiber Type:	OS2, G.657.B3, G.652.D
Fiber Core Diameter:	250 µm
Fiber Diameter:	900 µm
Fiber Count:	1
Fiber Color Coding:	TIA-598-D

**Outer Jacket Specifications**

Strength Member:	Aramid Yarns
Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.188 in (4.8 mm)
Color:	Lime Green

**Optical Characteristics**

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.5 dB/km	0.5 dB/km
Mode Field Diameter	9.2 µm	10.4 µm
1 Gigabit Ethernet Performance	5000 m	--
10 Gigabit Ethernet Performance	10000 m	50000 m

**Mechanical Characteristics**

Min. Bend Radius During Installation:	15X Cable OD
Min. Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	800 N (180 lbf)
Max. Tensile Strength During Operation:	240 N (54 lbf)
Crush Resistance:	100 N/cm
Bulk Cable Weight:	13.2 lbs/kft (19.6 kg/km)

**Temperature Range**

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-40°C to +70°C
Storage Temperature Range:	-40°C to +70°C

**Standards and Compliance**

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance
----------------------------	-------------------------------------

Flammability / Reaction to Fire:	UL 1666, UL 1685, FT4
NEC / UL Compliance:	OFNR
CEC / C(UL) Compliance:	OFNR
TIA/EIA Compliance:	598-D
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment)

History

Update and Revision:	Revision Number: 0.3 Revision Date: 07-10-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.