



**Product:** [FCSX12LKFMN](#)



FX ECX CASS OS2 12P MASS FUSION PIGTAIL LC KEYED DUPLEX

## Product Description

FX ECX CASSETTE, OS2, 12 PORTS, WITH 250um MASS FUSION RIBBON PIGTAILS, LC KEYED DUPLEX, RED ADAPTERS

## Technical Specifications

### Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

### Construction

#### Fiber Cable Construction

<b>Fiber Type</b>	OS2
Height:	1.300 in
Width:	6.340 in
Length:	8.740 in

### Physical Specifications

Max Capacity:	24 Fibers, 12 LC Duplex Ports
---------------	-------------------------------

### Mechanical Characteristics

Front Connection:	Static
-------------------	--------

### Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-10°C To +75°C

### Product Material

#### Materials

Description	Material	Color
Adapter Sleeve	Zirconia-Ceramic	
Front Connector Body	Plastic - UL94V-0	Red
Cassette Assembly	Plastic - UL94V-0	Black

### Transmission-Characteristics

#### Fiber Connector Performance

<b>Max. Insertion Loss</b>	<b>Min. Return Loss</b>
0.25 dB	-55 dB

### Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

## Related Part Numbers

Included Parts:	250um pigtails, splice sleeves and cable ties
-----------------	---

## Variants

Item #	Connector Type	Port Count
FCSX12LKFMA	LC Keyed Aqua	12 Port
FCSX12LKFMB	LC Keyed Blue	12 Port
FCSX12LKFMC	LC Keyed Green	12 Port
FCSX12LKFMD	LC Keyed Brown	12 Port
FCSX12LKFME	LC Keyed Black	12 Port
FCSX12LKFMF	LC Keyed Orange	12 Port
FCSX12LKFMG	LC Keyed Rose	12 Port
FCSX12LKFMH	LC Keyed Red	12 Port
FCSX12LKFMI	LC Keyed Gray	12 Port
FCSX12LKFMJ	LC Keyed Violet	12 Port
FCSX12LKFMK	LC Keyed White	12 Port
FCSX12LKFML	LC Keyed Yellow	12 Port

## Product Notes

Packaging:	Individually packaged in a plastic shell, shipped in cardboard box (12/box)
Notes:	Splice Holder is included. Splice holder is compatible with Belden Splice Sleeves part numbers (Post-Shrink Diameter): FXFUHS900AB25(2.5mm), FXFUHS9T2CB25 (2.0mm), FXFUHS250DB25 (1.5mm) and FXFUHSRIBEB12(Oval 4.1mmX4.6mm).

## History

Update and Revision:	Revision Number: 0.15 Revision Date: 02-12-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.