



**Product:** [FDSM048A2Y](#) 

Indoor/Outdoor Plenum OS2 Mini-Distribution 48 Fibers Aluminum Interlocked 3mm Sub-Units Yellow Jacket

## Product Description

FX Indoor/Outdoor, OS2, Mini-Distribution, 48 Fibers, OFCP Aluminum Interlocked Armor, 12F/Sub-Units (3.0MM), Yellow Jacket

## Technical Specifications

### Product Overview

Product Category:	Fiber Mini Distribution Cable
Suitable Applications:	Data Center, RAN, Horizontal Backbone, Premise Backbone, Patching, Trunking

### Fiber Specifications

Fiber Type:	OS2
Fiber Core Diameter:	8.2/125 $\mu\text{m}$
Fiber Diameter:	250 $\mu\text{m}$
Fiber Count:	48
Fiber Color Coding:	TIA-598-D

### Cable Construction

Number of Active Subunits:	4
Fibers Per Subunit:	12
Subunit Diameter:	0.118 in (3.0 mm)
Subunit Color:	Yellow
Fiber SubUnit Strength Members:	Waterblocking Aramid Yarns
Central Strength Member Type:	GRP
Cable Core Water Blocking:	Waterblock Tape

### Inner Jacket Specifications

Material:	PVC - Polyvinyl Chloride
Nominal Diameter@InnerJacket1 (cnv):	0.318 in (8.1 mm)
Color:	Yellow

### Armor Specifications

Armor Type and Material:	AIA - Aluminum Interlock Armor
--------------------------	--------------------------------

### Outer Jacket Specifications

Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.608 in (15.4 mm)
Outer Jacket Color:	Yellow

### Optical Characteristics

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.50 dB/km	0.50 dB/km
Mode Field Diameter	9.2 $\mu\text{m}$	10.4 $\mu\text{m}$
1 Gigabit Ethernet Performance	5,000 m	--
10 Gigabit Ethernet Performance	10,000 m	50,000 m

## Mechanical Characteristics

Minimum Bend Radius During Installation:	20x Cable OD
Minimum Bend Radius During Operation:	15x Cable OD
Max. Tensile Strength During Installation:	1800 N (405 lbf)
Max. Tensile Strength During Operation:	540 N (121 lbf)
Crush Resistance:	440 N/cm
Bulk Cable Weight:	229 lbs/kft (341 kg/km)

## Temperature Range

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-20°C to +70°C
Storage Temperature Range:	-40°C to +70°C

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance, UV Resistance
Sustainability:	CA Prop 65
NEC / UL Compliance:	OFCP
CEC / C(UL) Compliance:	OFCP
ICEA Compliance:	S-104-696
TIA/EIA Compliance:	598-D
Telcordia Compliance:	GR-409
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment)

## History

Update and Revision:	Revision Number: 0.7 Revision Date: 12-04-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color
FDMS048A2Y	Yellow

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.