



**Product:** [FD2H0365E](#)

Indoor/Outdoor Riser Heavy Duty Loose Tube OM2 36 Fibers

**Product Description**

FX Indoor/Outdoor Heavy Duty Loose Tube OM2 36 Fibers OFCR Corrugated Steel Tape Armor Sub-Units (6F) Gel Black

**Technical Specifications**

**Product Overview**

Construction Type:	Multi Loose Tube
Print Legend:	BELDEN 36xOM2 IN/OUTDOOR ARMORED LOOSE TUBE CABLE FD2H0365F E95466(-PLANT ID) (UL) TYPE OFNR C(UL) ---FT4--- ROHS (LOT NUMBER) (MMYYYY DATE CODE) (SEQUENTIAL MATERIAL)
Environmental Space:	Indoor/Outdoor
Suitable Applications:	Indoor/Outdoor

**Construction**

**Fiber Cable Construction**

Fiber Type	Fiber Count
OM2	36

Fiber Color Coding:	Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua
---------------------	---

**Buffer Specification**

Buffer Material
Loose tube - Gel-filled

Central Strength Member:	GRP
Cable Core Water Blocking:	Waterblocking Tape
Bulk Cable Weight:	15 lbs/1000ft
Weight:	150 kg

**SubUnit Specifications**

Number of Active Subunits:	6
Number of Subunit Positions:	6
Fibers Per Subunit:	6
Subunit Diameter:	0.110 in (2.8 mm)
Subunit Waterblocking:	Gel Filled

**Jacket Specifications**

Number of Jackets:	Double Jacket
Type of Armor:	Corrugated Steel Tape

**Inner Jacket**

Number of Ripcords:	2
Color:	Black
Material:	PVC - Polyvinyl Chloride

**Outer Jacket**

## Outer Jacket Material

Material	Nominal Diameter
Thermoplastic	0.63 in (16 mm)
Color:	Black
Number of Ripcords:	2
Nominal Diameter:	.54 (13.7)

## Optical Characteristics

Effective Modal Bandwidth (EMB):	950 MHz-km / 500 MHz-km
Fiber Core Diameter:	50/125µm
Max Attenuation at 1300 nm:	1.0 dB/km
Max Attenuation at 850 nm:	3.0 dB/km
Wavelength:	850 nm / 1300 nm
10 Gigabit Ethernet Performance:	150 m / 300 m
1 Gigabit Ethernet Performance:	550 m / 550 m
Min Overfilled Launch (OFL) Bandwidth:	700 MHz-km / 500 MHz-km

## Mechanical Characteristics

Crush Resistance:	440
-------------------	-----

## Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	20x Cable OD
Cable Min. Bend Radius Operation (Long Term)	15x Cable OD
Cable Max. Tensile Strength Installation (Short Term)	135 N (600 lbf)
Cable Max. Tensile Strength Operation (Long Term)	40 N (180 lbf)
Cable Impact Resistance	2.9 N/cm

## Temperature Range

Operating Temp Range:	-40C to +70C
Installation Temp Range:	-30C to +60C
Storage Temp Range:	-40C to +80C

## Standards

UL Rating/Flame Test:	Riser
UL Flammability:	OFRC
C (UL) US:	FT4
TIA/EIA Compliance:	ANSI/ICEA S-104-696
RoHS:	Yes

## Part Number

### Variants

Item #	Color	UPC
FD2H0365F	Black	612825388531

## History

Update and Revision:	Revision Number: 0.70 Revision Date: 06-01-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.