



Product: [FI1M024A8](#) 

Indoor Mini-Distribution OM1 24 Fibers OFCP Aluminum Interlocked Armor Sub-Units 2.0mm (8F)

Product Description

FX Indoor, Mini-Distribution, OM1, 24 Fibers, OFCP Aluminum Interlocked Armor, Sub-Units 2.0mm (8F), Orange Jacket

Technical Specifications

Product Overview

Product Category:	Fiber Mini Distribution Cable
Suitable Applications:	Data Center, RAN, Horizontal Backbone, Premise Backbone, Patching, Trunking

Fiber Specifications

Fiber Type:	OM1
Fiber Core Diameter:	62.5/125 µm
Fiber Diameter:	250 µm
Fiber Count:	24
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	3
Number of Fillers:	1
Fibers Per Subunit:	8
Subunit Diameter:	0.078 in (2.0 mm)
Subunit Color:	Orange
Fiber SubUnit Strength Members:	Aramid Yarns
Central Strength Member Type:	GRP

Inner Jacket Specifications

Inner Jacket Strength Member:	Aramid Yarns
Material:	PVC - Polyvinyl Chloride
Nominal Diameter@InnerJacket1 (cnv):	0.272 in (6.9 mm)
Color:	Orange
Number of Inner Jacket Ripcoords:	1

Armor Specifications

Armor Type and Material:	AIA - Aluminum Interlock Armor
--------------------------	--------------------------------

Outer Jacket Specifications

Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.561 in (14.2 mm)
Outer Jacket Color:	Orange

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.5 dB/km	1.25 dB/km
10 Gigabit Ethernet Performance	33 m	--

Min. Overfilled Launch (OFL) Bandwidth	200 MHz.km	500 MHz.km
--	------------	------------

Mechanical Characteristics

Minimum Bend Radius During Installation:	20x Cable OD
Minimum Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	660 N (150 lbf)
Max. Tensile Strength During Operation:	200 N (45 lbf)
Crush Resistance:	440 N/cm
Bulk Cable Weight:	105 lbs/kft (156 kg/km)

Temperature Range

Installation Temperature Range:	0°C to +60°C
Operating Temperature Range:	0°C to +70°C
Storage Temperature Range:	-40°C to +70°C

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	NFPA 262
NEC / UL Compliance:	OFCP
CEC / C(UL) Compliance:	FT6
ICEA Compliance:	S-83-596
TIA/EIA Compliance:	568.3, 598-D
Telcordia Compliance:	GR-409
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment)

History

Update and Revision:	Revision Number: 0.4 Revision Date: 06-26-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type
F11M024A8	Orange	Reel

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.