



Product: [FI2B006PB](#)

Indoor Plenum OM2 Breakout 6F 2mm Sub-Units Orange

Product Description

FX Indoor OM2 Breakout 6 Fibers OFNP Sub-Units (2.0MM) Orange Jacket

Technical Specifications

Product Overview

Construction Type:	Breakout
Environmental Space:	Indoor
Suitable Applications:	Indoor

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OM2	6

Fiber Color Coding:	Blue, Orange, Green, Brown, Gray, White
---------------------	---

Buffer Specification

Buffer Diameter
900 μ m

Bulk Cable Weight:	41 lbs/1000ft
--------------------	---------------

SubUnit Specifications

Fibers Per Subunit:	1
Subunit Diameter:	0.078 in (2.0 mm)

Outer Jacket

Outer Jacket Material

Nominal Diameter
0.31 in (7.9 mm)

Color:	Orange
Number of Ripcords:	2

Optical Characteristics

Effective Modal Bandwidth (EMB):	950 MHz-km / 500 MHz-km
Fiber Core Diameter:	50/125 μ m
Max Attenuation at 1300 nm:	1.25 dB/km
Max Attenuation at 850 nm:	3.5 dB/km
Wavelength:	850 nm / 1300 nm
10 Gigabit Ethernet Performance:	150 m / 300 m
1 Gigabit Ethernet Performance:	550 m / 550 m
Min Overfilled Launch (OFL) Bandwidth:	700 MHz-km / 500 MHz-km

Mechanical Characteristics

Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	20x Cable OD
Cable Min. Bend Radius Operation (Long Term)	10x Cable OD
Cable Max. Tensile Strength Installation (Short Term)	105 N (465 lbf)
Cable Max. Tensile Strength Operation (Long Term)	52 N (230 lbf)

Temperature Range

Storage Temp Range:	-40C to +70C
---------------------	--------------

Standards

UL Rating/Flame Test:	Plenum
NEC/(UL) Compliance:	OFNP
TIA/EIA Compliance:	ANSI/ICEA S-83-596
RoHS:	Yes

Part Number

Variants

Item #	Color	UPC
F12B006PB	Orange	612825369493

History

Update and Revision:	Revision Number: 0.54 Revision Date: 01-31-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.