



Product: [FDSH048LD](#)

Heavy Duty Indoor/Outdoor LSZH/OFNR OS2 Loose Tube 48 Fibers Dry

Product Description

FX Indoor/Outdoor, Heavy Duty Loose Tube, OS2, 48 Fibers, LSZH/OFNR, Sub-Units (12F), Dry, Black Jacket

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Product Category: | Fiber Multi-Loose Tube Cable |
| Suitable Applications: | Campus Area Network, Long Haul, Backbone |

Fiber Specifications

| | |
|----------------------|-----------------------|
| Fiber Type: | OS2 |
| Fiber Core Diameter: | 8.2/125 μm |
| Fiber Diameter: | 250 μm |
| Fiber Count: | 48 |
| Fiber Color Coding: | TIA-598-D |

Cable Construction

| | |
|----------------------------|-------------------|
| Number of Active Subunits: | 4 |
| Number of Fillers: | 1 |
| Fibers Per Subunit: | 12 |
| Subunit Waterblocking: | Gel Free |
| Subunit Diameter: | 0.098 in (2.5 mm) |
| Subunit Color: | TIA-598-D |
| Central Strength Member: | GRP |
| Cable Core Waterblocking: | Waterblock Tape |

Inner Jacket Specifications

| | |
|---------------------|---|
| Material: | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
| Nom. Diameter: | 0.355 in (9.0 mm) |
| Color: | Black |
| Number of Ripcords: | 1 |

Outer Jacket Specifications

| | |
|---------------------|---|
| Strength Member: | Waterblocking Fiberglass Yarns |
| Jacket Material: | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
| Nom. Diameter: | 0.515 in (13.1 mm) |
| Color: | Black |
| Number of Ripcords: | 1 |

Optical Characteristics

| Wavelength | 1310 nm | 1550 nm |
|---------------------|-------------------|--------------------|
| Max. Attenuation | 0.35 dB/km | 0.25 dB/km |
| Mode Field Diameter | 9.2 μm | 10.4 μm |

| | | |
|---------------------------------|----------|----------|
| 1 Gigabit Ethernet Performance | 5,000 m | -- |
| 10 Gigabit Ethernet Performance | 10,000 m | 40,000 m |

Mechanical Characteristics

| | |
|--|-------------------------|
| Min. Bend Radius During Installation: | 15 x Cable OD |
| Min. Bend Radius During Operation: | 10 x Cable OD |
| Max. Tensile Strength During Installation: | 2670 N (600 lbf) |
| Max. Tensile Strength During Operation: | 800 N (180 lbf) |
| Crush Resistance: | 440 N/cm |
| Bulk Cable Weight: | 106 lbs/kft (162 kg/km) |

Temperature Range

| | |
|---------------------------------|----------------|
| Installation Temperature Range: | -30°C to +60°C |
| Operating Temperature Range: | -40°C to +70°C |
| Storage Temperature Range: | -40°C to +70°C |

Standards and Compliance

| | |
|----------------------------------|-------------------------------------|
| Environmental Suitability: | Indoor/Outdoor, Sunlight Resistance |
| Sustainability: | CA Prop 65 |
| Flammability / Reaction to Fire: | OFNR, FT4 |
| ICEA Compliance: | S-104-696 |
| TIA/EIA Compliance: | 598 |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.17 Revision Date: 01-09-2025 |
|----------------------|---|

Part Numbers

Variants

| Item # | Color | Putup Type |
|-----------|-------|------------|
| FDSH048LD | Black | Reel |

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.