



**Product:** [FDSR072R5](#)

Indoor/Outdoor OFNR OS2 Flexible Ribbon 72 Fibers 24F Subs

## Product Description

Indoor/Outdoor Riser OS2 Flexible Ribbon 72 Fibers 24F Subunit Black Jacket

## Technical Specifications

### Product Overview

Construction Type:	Jacketed Ribbon
Environmental Space:	Indoor/Outdoor
Suitable Applications:	Indoor/Outdoor

### Construction

#### Fiber Cable Construction

Fiber Type	Fiber Count
OS2	72
Central Strength Member:	GRP
Bulk Cable Weight:	52 lbs/1000ft

### SubUnit Specifications

Number of Active Subunits:	3
Number of Subunit Positions:	4
Fibers Per Subunit:	24
Subunit Diameter:	0.118 in (3.0 mm)

### Jacket Specifications

Number of Jackets:	Single Jacket
--------------------	---------------

### Inner Jacket

Material:	PVC - Polyvinyl Chloride
-----------	--------------------------

### Outer Jacket

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.38 in (9.7mm)
Color:	Black
Nominal Diameter:	0.38 in (9.7mm)

### Optical Characteristics

Mode Field Diameter:	9.2
Fiber Core Diameter:	8.2/125µm
Max Attenuation at 1310 nm:	0.5 dB/km
Max Attenuation at 1550 nm:	0.5 dB/km
Wavelength:	1310 nm / 1550 nm

10 Gigabit Ethernet Performance:	10,000 m / -
1 Gigabit Ethernet Performance:	5,000 m / -

## Mechanical Characteristics

### Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	15x Cable OD
Cable Min. Bend Radius Operation (Long Term)	10x Cable OD
Cable Max. Tensile Strength Installation (Short Term)	Error
Cable Max. Tensile Strength Operation (Long Term)	Error

### Temperature Range

Operating Temp Range:	0C to +70C
Installation Temp Range:	0C to +60C
Storage Temp Range:	-20C to +70C

### Standards

UL Rating/Flame Test:	OFNR
NEC/(UL) Compliance:	N/A
TIA/EIA Compliance:	EIA/TIA 568-A, GR-409-CORE, ICEA-S-104-696
RoHS:	Yes

### History

Update and Revision:	Revision Number: 0.6 Revision Date: 01-31-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.