



Product: [FI4B004PBA](#) 

Indoor Plenum OM4 Breakout 4F 2mm Sub-Units Aqua

Product Description

Indoor OM4 Breakout 4 Fibers OFNP Sub-Units (2.0mm) Aqua Jacket

Technical Specifications

Product Overview

Suitable Applications:	Horizontal Backbone
------------------------	---------------------

Fiber Specifications

Fiber Type:	OM4
Fiber Core Diameter:	50/125µm µm
Fiber Diameter:	250 µm
Buffer Material:	PVC - Polyvinyl Chloride
Buffer Diameter:	900 µm µm
Fiber Count:	4
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	4
Fibers Per Subunit:	1
Subunit Diameter:	0.078 in (2.0 mm)
Subunit Strength Members:	Aramid yarns
Central Strength Member:	GRP
Core Wrap:	Nomex Tape

Outer Jacket Specifications

Strength Member:	Aramid Yarns
Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.263 in (6.7 mm)
Color:	Aqua
Number of Ripcords:	2

Mechanical Characteristics

Min. Bend Radius During Installation:	15x Cable OD
Min. Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	1330 N (300 lbf)
Max. Tensile Strength During Operation:	400 N (90 lbf)
Crush Resistance:	100 N/cm
Bulk Cable Weight:	15 lbs/kft (23 kg/km)

Temperature Range

Installation Temperature Range:	-0°C to +60°C
Operating Temperature Range:	-0°C to +70°C

Storage Temperature Range:	-40°C to +70°C
----------------------------	----------------

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65, Product Lens™
Flammability / Reaction to Fire:	OFNP, FT6
ICEA Compliance:	S-83-596
TIA/EIA Compliance:	ANSI/ICEA S-83-596

History

Update and Revision:	Revision Number: 0.67 Revision Date: 04-08-2022
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	UPC
F14B004PBA	Aqua	Reel	612825369639

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.