



Product: [FI1I002L0](#)

Indoor LSZH/Riser OM1 Interconnect 2F DX DX MiniRound 2mm

Product Description

FX Indoor OM1 Interconnect 2 Fibers LSZH/OFNR DX DX Mini-Round 2.0MM (250UM) Orange Jacket

Technical Specifications

Product Overview

Suitable Applications:	Indoor
------------------------	--------

Fiber Specifications

Fiber Type:	OM1
Fiber Core Diameter:	62.5/125µm
Buffer Material:	LSZH
Fiber Count:	2
Fiber Color Coding:	Blue, Orange

Outer Jacket Specifications

Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Nominal Diameter:	0.079 in
Color:	Orange

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.5 dB/km	1.25 dB/km

Mechanical Characteristics

Min Bend Radius During Installation:	20x Cable OD
Min Bend Radius During Operation:	10x Cable OD
Max Tensile Strength During Installation:	50 lbf
Max Tensile Strength During Operation:	15 lbf
Bulk Cable Weight:	2 lbs/1000ft

Temperature Range

Installation Temp Range:	-10C to +60C
Operating Temp Range:	0C to +70C
Storage Temp Range:	-40C to +70C

Standards and Compliance

Environmental Suitability:	Indoor
NEC / UL Compliance:	OFNR
CEC / C(UL) Compliance:	FT4
TIA/EIA Compliance:	ANSI/ICEA S-83-596

History

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.