



Part Number: FI4M072L2A

Indoor Riser OM4 Mini-Distribution 72F Aqua

Product Description

Mini-Distribution Fiber Cable, OM4, Multimode, 72 Fibers, LSZH/Riser (OFNR), 3.0mm, Aqua Jacket

Technical Specifications

Product Overview

Part Number:	FI4M072L2A
Construction Type:	Mini Distribution
Environmental Space:	Indoor
Suitable Applications:	Indoor

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OM4	72

Fiber Type:	OM4
Fiber Count:	72

Buffer Specification

Fiber Type
OM4

Central Strength Member:	GRP
--------------------------	-----

SubUnit Specifications

Number of Active Subunits:	6
Number of Subunit Positions:	6
Fibers Per Subunit:	12
SubUnit Diameter:	0.118 in (3.0 mm)

Jacket Specifications

Number of Jackets:	Single Jacket
Material@InnerJacket1:	LSZH

Outer Jacket Material

Material	Nominal Diameter
Thermoplastic	0.44 in (11.2 mm)

Outer Jacket Color:	Aqua
Number of Outer Jacket Ripcords:	2
OuterJacket1, Nominal Diameter:	0.440 (11.2)

Optical Characteristics

Effective Modal Bandwidth (EMB):	4700 MHz-km / 500 MHz-km
Fiber Core Diameter:	50/125
Max Attenuation at 1300 nm:	1.0 dB/km

Max Attenuation at 850 nm:	3.0 dB/km
Wavelength:	850 nm / 1300 nm
10 Gigabit Ethernet Performance:	550 m / 300 m
1 Gigabit Ethernet Performance:	- / 550 m
Min Overfilled Launch (OFL) Bandwidth:	3500 MHz-km /550 Mhz-km

Mechanical Characteristics

Min Bend Radius During Installation:	20x Cable OD
Min Bend Radius During Operation:	15x Cable OD

Temperature Range

Operating Temp Range:	0C to +70C
Installation Temp Range:	0C to +60C
Storage Temp Range:	-40C to +70C

Standards

UL Rating/Flame Test:	OFNR
NEC/(UL) Specification:	N/A
C (UL) US:	FT4
Telecommunications Standards:	ANSI/ICEA S-83-596
RoHS:	Yes

History

Variants

Item #	Color	UPC
FI4M072L2A	Aqua	612825288824

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.