



Product: [FI5M012P0](#) 

Indoor Plenum OM5 Mini-Distribution 12 Fibers Lime Green Jacket

Product Description

FX Indoor, OM5, Mini-Distribution, 12 Fibers, OFNP, 4.8 mm (Double Jacket), Lime Green Jacket

Technical Specifications

Product Overview

Product Category:	Fiber Mini Distribution Cable
Suitable Applications:	Data Center, RAN, Horizontal Backbone, Premise Backbone, Patching, Trunking

Fiber Specifications

Fiber Type:	OM5
Fiber Core Diameter:	50/125 μm
Fiber Diameter:	250 μm
Fiber Count:	12
Fiber Color Coding:	TIA-598-D

Inner Jacket Specifications

Material:	Thermoplastic
Nominal Diameter@InnerJacket1 (cnv):	0.120 in (3.0 mm)
Color:	Lime Green

Outer Jacket Specifications

Jacket Material:	Thermoplastic
Nom. Diameter:	0.190 in (4.8 mm)
Outer Jacket Color:	Lime Green

Optical Characteristics

Wavelength	850 nm	953 nm	1300 nm
Max. Attenuation	3.0 dB/km	1.0 dB/km	1.0 dB/km
1 Gigabit Ethernet Performance			--
10 Gigabit Ethernet Performance	550 m	1100 m	1100 m
Min. Effective Modal Bandwidth (EMB)	4700 MHz.km	2470 MHz.km	--
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz.km	1850 MHz.km	500 MHz.km

Mechanical Characteristics

Minimum Bend Radius During Installation:	15x Cable OD
Minimum Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	660 N (150 lbf)
Max. Tensile Strength During Operation:	200 N (45 lbf)
Crush Resistance:	110 N/cm
Bulk Cable Weight:	17 lbs/1000ft (25 kg/km)

Temperature Range

Installation Temperature Range:	0°C to +60°C
---------------------------------	--------------

Operating Temperature Range:	0°C to +70°C
Storage Temperature Range:	-40°C to +70°C

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	OFNP, UL 910, FT6
NEC / UL Compliance:	OFNP
CEC / C(UL) Compliance:	OFNP
ICEA Compliance:	S-83-596
TIA/EIA Compliance:	ANSI/ICEA S-83-596
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.96 Revision Date: 10-15-2024
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.