



Product: [FRCP3YSNV](#)



Fiber Raceway Top Outlet, Vertical Drop, 4x4, Slotted Lid

Product Description

Fiber Raceway Top Outlet, Vertical Drop, 4x4, with Lid, Vertical, Yellow

Technical Specifications

Product Overview

Environmental Space:	Indoor
----------------------	--------

Construction

Weight:	0.925 lbs
Height:	8.267 in (209.982 mm)
Width:	10.984 in
Length:	5.118 in

Related Part Numbers

Variants

Item #	Color	Length
FRCP3YSNV	Yellow	5.118 in

Product Notes

Notes:	This Top Outlet Assembly, Vertical Outlet, Down, for optical fibre cords, allows individual cords to exit, vertically down, anywhere along a length of straight 100mm, 220mm & 300mm duct. The unit simply fits along the edge of the duct – ie the side of the duct is not specially prepared or cut. The exiting optical fibre cords are guided through an MBR of 30mm whilst completing this change of direction. The outlet curve has no ribs ie there is nothing to restrict the naturally occurring free flow of optical fibre cords. The outlet guide can be connected to 100mm duct, using a slotless joiner(A standard joiner can also be used). Alternatively, the 100mm outlet can be connected to any standard duct size, as required, using standard duct adapters. The Top Outlet Assembly comes with a screw, which acts as a stand - off from the side of the duct. For heavy duty applications, the unit can be mounted on a steel bracket , which is bolted to the central, mid area of the unit. The steel mounting bracket is available separately. The mounting bracket can be secured to any of the standard duct mounting items. This unit comes with a removable lid. Duct covers for 100mm, 220mm & 300mm duct, are available separately. These items cover the area of duct behind the Top Outlet Assembly.
--------	---

History

Update and Revision:	Revision Number: 0.202 Revision Date: 03-28-2024
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.